

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642707

Luminaire Tested: ML5615LSNFL259FS1E - 591WB - 1500LM - 3000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642707  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSNFL259FS1E - 591WB - 1500LM - 3000K  
Description: ML56 RR, 25D TIR OPTIC, 5" DEADFRONT TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1698.5 lumens  
Efficiency: N/A  
Efficacy: 99.3 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct


Input Watts (W): 17.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642707

CATALOG NUMBER: ML5615LSNFL259FS1E - 591WB - 1500LM - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P642707

CATALOG NUMBER: ML5615LSNFL259FS1E - 591WB - 1500LM - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75																			
5	92	84	78	74	90	83	77	73	81	76	73	79	75	72	78	74	71	70																			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	66																			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62																			
8	80	71	65	61	79	70	64	61	69	64	60	68	63	60	67	63	60	58																			
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56																			
10	73	64	58	55	72	64	58	55	63	58	54	62	58	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	337354
5°	307580
10°	225078
15°	128138
20°	78900
25°	64107
30°	52796
35°	42865
40°	34625
45°	27687
50°	18078
55°	7927
60°	5052
65°	4483
70°	4062
75°	3904
80°	4364
85°	4348

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 27687 cd/sqm



TEST NUMBER: P642707

CATALOG NUMBER: ML5615LSNFL259FS1E - 591WB - 1500LM - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	335.5	19.8
10°-20°	451.4	26.6
20°-30°	339.0	20.0
30°-40°	279.5	16.5
40°-50°	186.3	11.0
50°-60°	63.2	3.7
60°-70°	24.3	1.4
70°-80°	13.7	0.8
80°-90°	5.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1125.8	66.3
0°-40°	1405.3	82.7
0°-60°	1654.8	97.4
0°-90°	1698.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1698.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4274	
5°	3882	335
15°	1568	451
25°	736	339
35°	445	279
45°	248	186
55°	58	63
65°	24	24
75°	13	14
85°	5	6
90°	0	



TEST NUMBER: P642707

CATALOG NUMBER: ML5615LSNFL259FS1E - 591WB - 1500LM - 3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4273.5
2.5°	4185.5
5°	3881.5
7.5°	3393.5
10°	2807.9
12.5°	2155.1
15°	1567.9
17.5°	1163.2
20°	939.2
22.5°	822.4
25°	736.0
27.5°	652.8
30°	579.2
32.5°	508.8
35°	444.8
37.5°	387.2
40°	336.0
42.5°	289.6
45°	248.0
47.5°	193.6
50°	147.2
52.5°	100.8
55°	57.6
57.5°	38.4
60°	32.0
62.5°	28.8
65°	24.0
67.5°	20.8
70°	17.6
72.5°	14.4
75°	12.8
77.5°	11.2
80°	9.6
82.5°	8.0
85°	4.8
87.5°	3.2
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)