

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643016

Luminaire Tested: ML5615LSNFL259FS1E - 694WB - 1200LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643016
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSNFL259FS1E - 694WB - 1200LM - 2700K
Description: ML56 RR, 25D TIR OPTIC, 6" WHITE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1384.9 lumens
Efficiency: N/A
Efficacy: 103.3 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.43
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643016
CATALOG NUMBER: ML5615LSNFL259FS1E - 694WB - 1200LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P643016

CATALOG NUMBER: ML5615LSNFL259FS1E - 694WB - 1200LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 113 | 110 | 107 | 105 | 111 | 108 | 105 | 103 | 104 | 102 | 100 | 100 | 99 | 97 | 97 | 95 | 94 | 92 | | | | | | | | | | | | | | | | | | | |
| 2 | 107 | 102 | 97 | 94 | 105 | 100 | 96 | 93 | 97 | 93 | 91 | 94 | 91 | 89 | 91 | 89 | 87 | 85 | | | | | | | | | | | | | | | | | | | |
| 3 | 101 | 94 | 89 | 85 | 99 | 93 | 88 | 84 | 90 | 86 | 83 | 88 | 84 | 81 | 85 | 83 | 80 | 78 | | | | | | | | | | | | | | | | | | | |
| 4 | 96 | 88 | 82 | 78 | 94 | 87 | 81 | 77 | 85 | 80 | 76 | 82 | 78 | 75 | 81 | 77 | 74 | 73 | | | | | | | | | | | | | | | | | | | |
| 5 | 91 | 82 | 76 | 72 | 89 | 81 | 76 | 71 | 79 | 74 | 71 | 78 | 73 | 70 | 76 | 72 | 69 | 68 | | | | | | | | | | | | | | | | | | | |
| 6 | 87 | 77 | 71 | 67 | 85 | 77 | 71 | 66 | 75 | 70 | 66 | 74 | 69 | 66 | 72 | 68 | 65 | 64 | | | | | | | | | | | | | | | | | | | |
| 7 | 82 | 73 | 67 | 62 | 81 | 72 | 66 | 62 | 71 | 66 | 62 | 70 | 65 | 62 | 69 | 64 | 61 | 60 | | | | | | | | | | | | | | | | | | | |
| 8 | 79 | 69 | 63 | 59 | 77 | 69 | 63 | 59 | 67 | 62 | 58 | 66 | 62 | 58 | 65 | 61 | 58 | 57 | | | | | | | | | | | | | | | | | | | |
| 9 | 75 | 66 | 60 | 56 | 74 | 65 | 60 | 56 | 64 | 59 | 55 | 63 | 59 | 55 | 62 | 58 | 55 | 54 | | | | | | | | | | | | | | | | | | | |
| 10 | 72 | 63 | 57 | 53 | 71 | 62 | 57 | 53 | 61 | 56 | 53 | 61 | 56 | 53 | 60 | 56 | 52 | 51 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | 0° |
|-----|--------|
| 0° | 186367 |
| 5° | 170173 |
| 10° | 123511 |
| 15° | 70318 |
| 20° | 43071 |
| 25° | 34720 |
| 30° | 28327 |
| 35° | 22761 |
| 40° | 18005 |
| 45° | 14211 |
| 50° | 11104 |
| 55° | 8697 |
| 60° | 6929 |
| 65° | 5578 |
| 70° | 4055 |
| 75° | 2139 |
| 80° | 1610 |
| 85° | 818 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14211 cd/sqm



TEST NUMBER: P643016

CATALOG NUMBER: ML5615LSNFL259FS1E - 694WB - 1200LM - 2700K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 266.6 | 19.3 |
| 10°-20° | 356.8 | 25.8 |
| 20°-30° | 264.5 | 19.1 |
| 30°-40° | 213.5 | 15.4 |
| 40°-50° | 142.9 | 10.3 |
| 50°-60° | 82.9 | 6.0 |
| 60°-70° | 43.4 | 3.1 |
| 70°-80° | 12.6 | 0.9 |
| 80°-90° | 1.7 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 887.9 | 64.1 |
| 0°-40° | 1101.4 | 79.5 |
| 0°-60° | 1327.2 | 95.8 |
| 0°-90° | 1384.9 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1384.9 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 3400 | |
| 5° | 3092 | 267 |
| 15° | 1239 | 357 |
| 25° | 574 | 264 |
| 35° | 340 | 214 |
| 45° | 183 | 143 |
| 55° | 91 | 83 |
| 65° | 43 | 43 |
| 75° | 10 | 13 |
| 85° | 1 | 2 |
| 90° | 0 | |



TEST NUMBER: P643016

CATALOG NUMBER: ML5615LSNFL259FS1E - 694WB - 1200LM - 2700K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 3399.6 |
| 2.5° | 3328.8 |
| 5° | 3092.4 |
| 7.5° | 2697.9 |
| 10° | 2218.8 |
| 12.5° | 1709.3 |
| 15° | 1239.0 |
| 17.5° | 917.8 |
| 20° | 738.3 |
| 22.5° | 643.5 |
| 25° | 574.0 |
| 27.5° | 508.2 |
| 30° | 447.5 |
| 32.5° | 391.9 |
| 35° | 340.1 |
| 37.5° | 293.3 |
| 40° | 251.6 |
| 42.5° | 216.2 |
| 45° | 183.3 |
| 47.5° | 154.2 |
| 50° | 130.2 |
| 52.5° | 108.7 |
| 55° | 91.0 |
| 57.5° | 75.9 |
| 60° | 63.2 |
| 62.5° | 53.1 |
| 65° | 43.0 |
| 67.5° | 35.4 |
| 70° | 25.3 |
| 72.5° | 16.4 |
| 75° | 10.1 |
| 77.5° | 6.3 |
| 80° | 5.1 |
| 82.5° | 2.5 |
| 85° | 1.3 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)