

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642714

Luminaire Tested: ML5615LSNFL259FS1E - 591WB - 900LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642714
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSNFL259FS1E - 591WB - 900LM - 4000K
Description: ML56 RR, 25D TIR OPTIC, 5" DEADFRONT TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1207.3 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642714

CATALOG NUMBER: ML5615LSNFL259FS1E - 591WB - 900LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P642714

CATALOG NUMBER: ML5615LSNFL259FS1E - 591WB - 900LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75																			
5	92	84	78	74	90	83	77	73	81	76	73	79	75	72	78	74	71	70																			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	66																			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62																			
8	80	71	65	61	79	70	64	61	69	64	60	68	63	60	67	63	60	58																			
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56																			
10	73	64	58	55	72	64	58	55	63	58	54	62	58	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	239791
5°	218630
10°	159989
15°	91083
20°	56083
25°	45563
30°	37528
35°	30472
40°	24608
45°	19682
50°	12846
55°	5629
60°	3584
65°	3194
70°	2885
75°	2776
80°	3091
85°	3080

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19682 cd/sqm



TEST NUMBER: P642714

CATALOG NUMBER: ML5615LSNFL259FS1E - 591WB - 900LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	238.5	19.8
10°-20°	320.9	26.6
20°-30°	240.9	20.0
30°-40°	198.6	16.5
40°-50°	132.4	11.0
50°-60°	44.9	3.7
60°-70°	17.3	1.4
70°-80°	9.8	0.8
80°-90°	4.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	800.2	66.3
0°-40°	998.9	82.7
0°-60°	1176.2	97.4
0°-90°	1207.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1207.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3038	
5°	2759	238
15°	1114	321
25°	523	241
35°	316	199
45°	176	132
55°	41	45
65°	17	17
75°	9	10
85°	3	4
90°	0	



TEST NUMBER: P642714

CATALOG NUMBER: ML5615LSNFL259FS1E - 591WB - 900LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	3037.6
2.5°	2975.1
5°	2759.0
7.5°	2412.1
10°	1995.9
12.5°	1531.9
15°	1114.5
17.5°	826.8
20°	667.6
22.5°	584.5
25°	523.1
27.5°	464.0
30°	411.7
32.5°	361.6
35°	316.2
37.5°	275.2
40°	238.8
42.5°	205.8
45°	176.3
47.5°	137.6
50°	104.6
52.5°	71.6
55°	40.9
57.5°	27.3
60°	22.7
62.5°	20.5
65°	17.1
67.5°	14.8
70°	12.5
72.5°	10.2
75°	9.1
77.5°	8.0
80°	6.8
82.5°	5.7
85°	3.4
87.5°	2.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)