

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643079

Luminaire Tested: ML5615LSVWFL759FS1E - 592SC - 1200LM - 4000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P643079  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-71)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSVWFL759FS1E - 592SC - 1200LM - 4000K  
Description: ML56 RR, 75D TIR OPTIC, 5" SPECULAR CLEAR TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1561.4 lumens  
Efficiency: N/A  
Efficacy: 116.5 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.07  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct


Input Watts (W): 13.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P643079

CATALOG NUMBER: ML5615LSVWFL759FS1E - 592SC - 1200LM - 4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P643079

CATALOG NUMBER: ML5615LSVWFL759FS1E - 592SC - 1200LM - 4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93	93	93	93
2	107	102	97	93	105	100	96	92	96	93	90	93	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78	78	78	78
4	95	87	81	76	93	85	80	75	83	78	75	81	77	74	79	76	73	71	71	71	71
5	89	80	74	69	88	79	73	69	77	72	68	76	71	68	74	70	67	65	65	65	65
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60	60	60	60
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55	55	55	55
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51	51	51	51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48	48	48	48
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44	44	44	44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	92385
5°	92397
10°	94275
15°	96943
20°	95903
25°	90795
30°	82038
35°	65810
40°	43858
45°	22149
50°	12355
55°	7322
60°	2731
65°	542
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 22149 cd/sqm



TEST NUMBER: P643079

CATALOG NUMBER: ML5615LSVWFL759FS1E - 592SC - 1200LM - 4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	111.7	7.2
10°-20°	332.7	21.3
20°-30°	475.6	30.5
30°-40°	417.9	26.8
40°-50°	169.3	10.8
50°-60°	49.0	3.1
60°-70°	5.2	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	920.0	58.9
0°-40°	1337.9	85.7
0°-60°	1556.2	99.7
0°-90°	1561.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1561.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1170	
5°	1166	112
15°	1186	333
25°	1042	476
35°	683	418
45°	198	169
55°	53	49
65°	3	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P643079

CATALOG NUMBER: ML5615LSVWFL759FS1E - 592SC - 1200LM - 4000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1170.3
2.5°	1170.3
5°	1166.0
7.5°	1168.9
10°	1176.1
12.5°	1184.7
15°	1186.2
17.5°	1171.8
20°	1141.6
22.5°	1097.0
25°	1042.4
27.5°	977.7
30°	900.0
32.5°	800.8
35°	682.9
37.5°	552.1
40°	425.6
42.5°	300.5
45°	198.4
47.5°	130.8
50°	100.6
52.5°	74.8
55°	53.2
57.5°	34.5
60°	17.3
62.5°	8.6
65°	2.9
67.5°	1.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)