

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642722

Luminaire Tested: ML5615LSNFL259FS1E - 592H - 1500LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642722
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSNFL259FS1E - 592H - 1500LM - 3000K
Description: ML56 RR, 25D TIR OPTIC, 5" HAZE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1682.5 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642722

CATALOG NUMBER: ML5615LSNFL259FS1E - 592H - 1500LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P642722

CATALOG NUMBER: ML5615LSNFL259FS1E - 592H - 1500LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 114 | 111 | 109 | 107 | 112 | 109 | 107 | 105 | 105 | 104 | 102 | 101 | 100 | 99 | 98 | 97 | 96 | 94 | | | | | | | | | | | | | | | | | | | |
| 2 | 109 | 104 | 101 | 97 | 107 | 103 | 99 | 96 | 99 | 97 | 94 | 96 | 94 | 92 | 94 | 92 | 90 | 89 | | | | | | | | | | | | | | | | | | | |
| 3 | 104 | 98 | 93 | 90 | 102 | 97 | 92 | 89 | 94 | 90 | 88 | 92 | 89 | 86 | 89 | 87 | 85 | 83 | | | | | | | | | | | | | | | | | | | |
| 4 | 99 | 92 | 87 | 83 | 97 | 91 | 86 | 83 | 89 | 85 | 82 | 87 | 84 | 81 | 85 | 82 | 80 | 79 | | | | | | | | | | | | | | | | | | | |
| 5 | 95 | 87 | 82 | 78 | 93 | 86 | 81 | 77 | 84 | 80 | 77 | 83 | 79 | 76 | 81 | 78 | 75 | 74 | | | | | | | | | | | | | | | | | | | |
| 6 | 91 | 82 | 77 | 73 | 89 | 82 | 77 | 73 | 80 | 76 | 72 | 79 | 75 | 72 | 78 | 74 | 71 | 70 | | | | | | | | | | | | | | | | | | | |
| 7 | 87 | 78 | 73 | 69 | 86 | 78 | 72 | 69 | 76 | 72 | 68 | 75 | 71 | 68 | 74 | 71 | 68 | 66 | | | | | | | | | | | | | | | | | | | |
| 8 | 83 | 75 | 69 | 65 | 82 | 74 | 69 | 65 | 73 | 68 | 65 | 72 | 68 | 65 | 71 | 67 | 64 | 63 | | | | | | | | | | | | | | | | | | | |
| 9 | 80 | 71 | 66 | 62 | 79 | 71 | 65 | 62 | 70 | 65 | 62 | 69 | 65 | 62 | 68 | 64 | 61 | 60 | | | | | | | | | | | | | | | | | | | |
| 10 | 77 | 68 | 63 | 59 | 76 | 68 | 63 | 59 | 67 | 62 | 59 | 66 | 62 | 59 | 65 | 61 | 59 | 57 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 354311 |
| 5° | 324704 |
| 10° | 241815 |
| 15° | 144213 |
| 20° | 91467 |
| 25° | 72242 |
| 30° | 56925 |
| 35° | 44600 |
| 40° | 33162 |
| 45° | 18588 |
| 50° | 4716 |
| 55° | 2422 |
| 60° | 1768 |
| 65° | 598 |
| 70° | 369 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18588 cd/sqm



TEST NUMBER: P642722

CATALOG NUMBER: ML5615LSNFL259FS1E - 592H - 1500LM - 3000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 355.9 | 21.2 |
| 10°-20° | 504.5 | 30.0 |
| 20°-30° | 381.4 | 22.7 |
| 30°-40° | 290.2 | 17.3 |
| 40°-50° | 127.6 | 7.6 |
| 50°-60° | 17.9 | 1.1 |
| 60°-70° | 4.3 | 0.3 |
| 70°-80° | 0.6 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1241.8 | 73.8 |
| 0°-40° | 1532.1 | 91.1 |
| 0°-60° | 1677.6 | 99.7 |
| 0°-90° | 1682.5 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1682.5 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 4488 | |
| 5° | 4098 | 356 |
| 15° | 1765 | 504 |
| 25° | 829 | 381 |
| 35° | 463 | 290 |
| 45° | 166 | 128 |
| 55° | 18 | 18 |
| 65° | 3 | 4 |
| 75° | 0 | 1 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P642722

CATALOG NUMBER: ML5615LSNFL259FS1E - 592H - 1500LM - 3000K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 4488.3 |
| 2.5° | 4400.2 |
| 5° | 4097.6 |
| 7.5° | 3609.2 |
| 10° | 3016.7 |
| 12.5° | 2361.8 |
| 15° | 1764.6 |
| 17.5° | 1341.8 |
| 20° | 1088.8 |
| 22.5° | 944.7 |
| 25° | 829.4 |
| 27.5° | 719.0 |
| 30° | 624.5 |
| 32.5° | 538.0 |
| 35° | 462.8 |
| 37.5° | 397.1 |
| 40° | 321.8 |
| 42.5° | 240.2 |
| 45° | 166.5 |
| 47.5° | 88.1 |
| 50° | 38.4 |
| 52.5° | 24.0 |
| 55° | 17.6 |
| 57.5° | 14.4 |
| 60° | 11.2 |
| 62.5° | 6.4 |
| 65° | 3.2 |
| 67.5° | 1.6 |
| 70° | 1.6 |
| 72.5° | 1.6 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)