

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642725

Luminaire Tested: ML5615LSNFL259FS1E - 592H - 1500LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642725
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSNFL259FS1E - 592H - 1500LM - 5000K
Description: ML56 RR, 25D TIR OPTIC, 5" HAZE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1860.4 lumens
Efficiency: N/A
Efficacy: 108.8 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642725

CATALOG NUMBER: ML5615LSNFL259FS1E - 592H - 1500LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P642725

CATALOG NUMBER: ML5615LSNFL259FS1E - 592H - 1500LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94																			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89																			
3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83																			
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79																			
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74																			
6	91	82	77	73	89	82	77	73	80	76	72	79	75	72	78	74	71	70																			
7	87	78	73	69	86	78	72	69	76	72	68	75	71	68	74	71	68	66																			
8	83	75	69	65	82	74	69	65	73	68	65	72	68	65	71	67	64	63																			
9	80	71	66	62	79	71	65	62	70	65	62	69	65	62	68	64	61	60																			
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	61	59	57																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	391744
5°	359008
10°	267369
15°	159447
20°	101136
25°	79881
30°	62941
35°	49312
40°	36676
45°	20553
50°	5219
55°	2684
60°	1958
65°	654
70°	415
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20553 cd/sqm



TEST NUMBER: P642725

CATALOG NUMBER: ML5615LSNFL259FS1E - 592H - 1500LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	393.5	21.2
10°-20°	557.8	30.0
20°-30°	421.7	22.7
30°-40°	320.9	17.3
40°-50°	141.1	7.6
50°-60°	19.8	1.1
60°-70°	4.8	0.3
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1373.0	73.8
0°-40°	1694.0	91.1
0°-60°	1854.9	99.7
0°-90°	1860.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1860.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4962	
5°	4530	394
15°	1951	558
25°	917	422
35°	512	321
45°	184	141
55°	20	20
65°	4	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P642725

CATALOG NUMBER: ML5615LSNFL259FS1E - 592H - 1500LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	4962.5
2.5°	4865.2
5°	4530.5
7.5°	3990.6
10°	3335.5
12.5°	2611.4
15°	1951.0
17.5°	1483.6
20°	1203.9
22.5°	1044.6
25°	917.1
27.5°	794.9
30°	690.5
32.5°	594.9
35°	511.7
37.5°	439.1
40°	355.9
42.5°	265.6
45°	184.1
47.5°	97.4
50°	42.5
52.5°	26.6
55°	19.5
57.5°	15.9
60°	12.4
62.5°	7.1
65°	3.5
67.5°	1.8
70°	1.8
72.5°	1.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)