

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643094

Luminaire Tested: ML5615LSVWFL759FS1E - 592W - 1200LM - 4000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P643094  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSVWFL759FS1E - 592W - 1200LM - 4000K  
Description: ML56 RR, 75D TIR OPTIC, 5" WHITE TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1549.9 lumens  
Efficiency: N/A  
Efficacy: 115.7 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.09  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P643094  
CATALOG NUMBER: ML5615LSVWFL759FS1E - 592W - 1200LM - 4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P643094

CATALOG NUMBER: ML5615LSVWFL759FS1E - 592W - 1200LM - 4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	87	85	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	58	58	58	58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54	54	54	54
8	74	63	57	52	73	63	56	52	62	56	52	61	55	51	59	55	51	50	50	50	50
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	48	46	46	46	46
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43	43	43	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	84285
5°	85518
10°	88118
15°	91484
20°	92593
25°	88243
30°	79376
35°	64114
40°	43539
45°	22618
50°	13767
55°	9097
60°	4768
65°	2690
70°	2654
75°	2623
80°	2591
85°	2627

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 22618 cd/sqm



TEST NUMBER: P643094

CATALOG NUMBER: ML5615LSVWFL759FS1E - 592W - 1200LM - 4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.7	6.7
10°-20°	315.4	20.4
20°-30°	461.4	29.8
30°-40°	407.0	26.3
40°-50°	173.1	11.2
50°-60°	60.1	3.9
60°-70°	17.2	1.1
70°-80°	9.1	0.6
80°-90°	3.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	880.4	56.8
0°-40°	1287.4	83.1
0°-60°	1520.5	98.1
0°-90°	1549.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1549.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1068	
5°	1079	104
15°	1119	315
25°	1013	461
35°	665	407
45°	203	173
55°	66	60
65°	14	17
75°	9	9
85°	3	3
90°	0	



TEST NUMBER: P643094

CATALOG NUMBER: ML5615LSVWFL759FS1E - 592W - 1200LM - 4000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1067.7
2.5°	1070.6
5°	1079.2
7.5°	1089.2
10°	1099.3
12.5°	1109.4
15°	1119.4
17.5°	1119.4
20°	1102.2
22.5°	1066.2
25°	1013.1
27.5°	948.4
30°	870.8
32.5°	773.1
35°	665.3
37.5°	541.7
40°	422.5
42.5°	300.3
45°	202.6
47.5°	140.8
50°	112.1
52.5°	86.2
55°	66.1
57.5°	47.4
60°	30.2
62.5°	21.6
65°	14.4
67.5°	12.9
70°	11.5
72.5°	10.1
75°	8.6
77.5°	7.2
80°	5.7
82.5°	4.3
85°	2.9
87.5°	1.4
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)