

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642731

Luminaire Tested: ML5615LSNFL259FS1E - 592SC - 1200LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642731  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-2)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSNFL259FS1E - 592SC - 1200LM - 2700K  
Description: ML56 RR, 25D TIR OPTIC, 5" SPECULAR CLEAR TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1345.7 lumens  
Efficiency: N/A  
Efficacy: 100.4 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.48  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct


Input Watts (W): 13.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642731

CATALOG NUMBER: ML5615LSNFL259FS1E - 592SC - 1200LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P642731

CATALOG NUMBER: ML5615LSNFL259FS1E - 592SC - 1200LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89			
3	104	98	93	90	102	97	92	89	94	91	88	92	89	86	89	87	85	83			
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79			
5	95	87	82	78	93	86	81	78	85	80	77	83	79	76	81	78	76	74			
6	91	83	77	73	89	82	77	73	80	76	72	79	75	72	78	74	71	70			
7	87	78	73	69	86	78	73	69	76	72	69	75	71	68	74	71	68	67			
8	83	75	69	65	82	74	69	65	73	68	65	72	68	65	71	67	64	63			
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	60			
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	62	59	58			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	277801
5°	254495
10°	191203
15°	119033
20°	77177
25°	57644
30°	43599
35°	34510
40°	26340
45°	15261
50°	4040
55°	1748
60°	1200
65°	467
70°	300
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 15261 cd/sqm



TEST NUMBER: P642731

CATALOG NUMBER: ML5615LSNFL259FS1E - 592SC - 1200LM - 2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	279.8	20.8
10°-20°	414.2	30.8
20°-30°	305.8	22.7
30°-40°	224.3	16.7
40°-50°	104.4	7.8
50°-60°	13.7	1.0
60°-70°	3.3	0.2
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	999.8	74.3
0°-40°	1224.1	91.0
0°-60°	1342.3	99.7
0°-90°	1345.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1345.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3519	
5°	3212	280
15°	1456	414
25°	662	306
35°	358	224
45°	137	104
55°	13	14
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P642731

CATALOG NUMBER: ML5615LSNFL259FS1E - 592SC - 1200LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3519.1
2.5°	3450.8
5°	3211.6
7.5°	2838.3
10°	2385.3
12.5°	1898.1
15°	1456.5
17.5°	1141.4
20°	918.7
22.5°	774.4
25°	661.8
27.5°	559.3
30°	478.3
32.5°	411.3
35°	358.1
37.5°	308.8
40°	255.6
42.5°	193.6
45°	136.7
47.5°	77.2
50°	32.9
52.5°	19.0
55°	12.7
57.5°	10.1
60°	7.6
62.5°	5.1
65°	2.5
67.5°	1.3
70°	1.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)