

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642738

Luminaire Tested: ML5615LSNFL259FS1E - 592SC - 1500LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642738
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSNFL259FS1E - 592SC - 1500LM - 3500K
Description: ML56 RR, 25D TIR OPTIC, 5" SPECULAR CLEAR TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1748.0 lumens
Efficiency: N/A
Efficacy: 102.2 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.48
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642738

CATALOG NUMBER: ML5615LSNFL259FS1E - 592SC - 1500LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P642738

CATALOG NUMBER: ML5615LSNFL259FS1E - 592SC - 1500LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94																			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89																			
3	104	98	93	90	102	97	92	89	94	91	88	92	89	86	89	87	85	83																			
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79																			
5	95	87	82	78	93	86	81	78	85	80	77	83	79	76	81	78	76	74																			
6	91	83	77	73	89	82	77	73	80	76	72	79	75	72	78	74	71	70																			
7	87	78	73	69	86	78	73	69	77	72	69	75	71	68	74	71	68	67																			
8	83	75	69	65	82	74	69	65	73	68	65	72	68	65	71	67	64	63																			
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	60																			
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	62	59	58																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	360855
5°	330584
10°	248364
15°	154617
20°	100246
25°	74881
30°	56633
35°	44831
40°	34213
45°	19816
50°	5244
55°	2257
60°	1563
65°	616
70°	369
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19816 cd/sqm



TEST NUMBER: P642738

CATALOG NUMBER: ML5615LSNFL259FS1E - 592SC - 1500LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	363.4	20.8
10°-20°	538.1	30.8
20°-30°	397.3	22.7
30°-40°	291.4	16.7
40°-50°	135.6	7.8
50°-60°	17.8	1.0
60°-70°	4.2	0.2
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1298.7	74.3
0°-40°	1590.1	91.0
0°-60°	1743.6	99.7
0°-90°	1748.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1748.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4571	
5°	4172	363
15°	1892	538
25°	860	397
35°	465	291
45°	178	136
55°	16	18
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P642738

CATALOG NUMBER: ML5615LSNFL259FS1E - 592SC - 1500LM - 3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	4571.2
2.5°	4482.4
5°	4171.8
7.5°	3686.9
10°	3098.4
12.5°	2465.6
15°	1891.9
17.5°	1482.6
20°	1193.3
22.5°	1006.0
25°	859.7
27.5°	726.5
30°	621.3
32.5°	534.2
35°	465.2
37.5°	401.1
40°	332.0
42.5°	251.5
45°	177.5
47.5°	100.3
50°	42.7
52.5°	24.7
55°	16.4
57.5°	13.1
60°	9.9
62.5°	6.6
65°	3.3
67.5°	1.6
70°	1.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)