

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642765

Luminaire Tested: ML5615LSNFL259FS1E - 593BB - 1200LM - 5000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642765  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSNFL259FS1E - 593BB - 1200LM - 5000K  
Description: ML56 RR, 25D TIR OPTIC, 5" BLACK BAFFLE TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1376.9 lumens  
Efficiency: N/A  
Efficacy: 102.8 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.43  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642765  
CATALOG NUMBER: ML5615LSNFL259FS1E - 593BB - 1200LM - 5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P642765

CATALOG NUMBER: ML5615LSNFL259FS1E - 593BB - 1200LM - 5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	94			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89			
3	104	98	93	90	102	97	92	89	94	91	88	92	89	86	89	87	85	83			
4	99	92	87	83	98	91	86	83	89	85	82	87	84	81	85	82	80	79			
5	95	87	82	78	93	86	81	78	85	80	77	83	79	76	81	78	76	74			
6	91	83	77	73	89	82	77	73	80	76	72	79	75	72	78	74	72	70			
7	87	78	73	69	86	78	73	69	77	72	69	75	71	68	74	71	68	67			
8	83	75	69	66	82	74	69	65	73	68	65	72	68	65	71	67	65	63			
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	62	60			
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	58			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	304822
5°	277935
10°	202930
15°	115266
20°	70247
25°	56790
30°	46051
35°	37035
40°	28473
45°	16389
50°	3893
55°	1789
60°	1358
65°	542
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 16389 cd/sqm



TEST NUMBER: P642765

CATALOG NUMBER: ML5615LSNFL259FS1E - 593BB - 1200LM - 5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	303.3	22.0
10°-20°	405.4	29.4
20°-30°	299.8	21.8
30°-40°	240.6	17.5
40°-50°	111.1	8.1
50°-60°	13.7	1.0
60°-70°	3.2	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1008.4	73.2
0°-40°	1249.0	90.7
0°-60°	1373.8	99.8
0°-90°	1376.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1376.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3861	
5°	3507	303
15°	1410	405
25°	652	300
35°	384	241
45°	147	111
55°	13	14
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P642765

CATALOG NUMBER: ML5615LSNFL259FS1E - 593BB - 1200LM - 5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3861.4
2.5°	3779.4
5°	3507.4
7.5°	3075.6
10°	2531.6
12.5°	1932.9
15°	1410.4
17.5°	1044.9
20°	836.2
22.5°	729.7
25°	652.0
27.5°	575.7
30°	505.2
32.5°	441.8
35°	384.3
37.5°	332.5
40°	276.3
42.5°	205.8
45°	146.8
47.5°	80.6
50°	31.7
52.5°	18.7
55°	13.0
57.5°	10.1
60°	8.6
62.5°	4.3
65°	2.9
67.5°	1.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)