

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642766

Luminaire Tested: ML5615LSNFL259FS1E - 593BB - 1500LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642766  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSNFL259FS1E - 593BB - 1500LM - 2700K  
Description: ML56 RR, 25D TIR OPTIC, 5" BLACK BAFFLE TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1488.5 lumens  
Efficiency: N/A  
Efficacy: 87.0 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.43  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct

Input Watts (W): 17.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642766  
CATALOG NUMBER: ML5615LSNFL259FS1E - 593BB - 1500LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P642766

CATALOG NUMBER: ML5615LSNFL259FS1E - 593BB - 1500LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	94																			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89																			
3	104	98	93	90	102	97	92	89	94	91	88	92	89	86	89	87	85	83																			
4	99	92	87	83	98	91	86	83	89	85	82	87	84	81	85	82	80	79																			
5	95	87	82	78	93	86	81	78	85	80	77	83	79	76	81	78	76	74																			
6	91	83	77	73	89	82	77	73	80	76	72	79	75	72	78	74	72	70																			
7	87	78	73	69	86	78	73	69	77	72	69	75	71	68	74	71	68	67																			
8	83	75	69	66	82	74	69	65	73	68	65	72	68	65	71	67	65	63																			
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	62	60																			
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	58																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	329531
5°	300456
10°	219378
15°	124607
20°	75942
25°	61389
30°	49779
35°	40032
40°	30781
45°	17717
50°	4200
55°	1927
60°	1468
65°	579
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 17717 cd/sqm



TEST NUMBER: P642766

CATALOG NUMBER: ML5615LSNFL259FS1E - 593BB - 1500LM - 2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	327.9	22.0
10°-20°	438.2	29.4
20°-30°	324.0	21.8
30°-40°	260.1	17.5
40°-50°	120.1	8.1
50°-60°	14.8	1.0
60°-70°	3.4	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1090.1	73.2
0°-40°	1350.2	90.7
0°-60°	1485.1	99.8
0°-90°	1488.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1488.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4174	
5°	3792	328
15°	1525	438
25°	705	324
35°	415	260
45°	159	120
55°	14	15
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P642766

CATALOG NUMBER: ML5615LSNFL259FS1E - 593BB - 1500LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4174.4
2.5°	4085.7
5°	3791.6
7.5°	3324.9
10°	2736.8
12.5°	2089.5
15°	1524.7
17.5°	1129.6
20°	904.0
22.5°	788.8
25°	704.8
27.5°	622.3
30°	546.1
32.5°	477.6
35°	415.4
37.5°	359.4
40°	298.7
42.5°	222.5
45°	158.7
47.5°	87.1
50°	34.2
52.5°	20.2
55°	14.0
57.5°	10.9
60°	9.3
62.5°	4.7
65°	3.1
67.5°	1.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)