

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643170

Luminaire Tested: ML5615LSVWFL759FS1E - 594SNB - 1200LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643170
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-79)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL759FS1E - 594SNB - 1200LM - 5000K
Description: ML56 RR, 75D TIR OPTIC, 5" SATIN NICKLE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1577.9 lumens
Efficiency: N/A
Efficacy: 117.8 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.09
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643170
CATALOG NUMBER: ML5615LSVWFL759FS1E - 594SNB - 1200LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P643170

CATALOG NUMBER: ML5615LSVWFL759FS1E - 594SNB - 1200LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20										
RC	80					70					50					30					10					0					
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0				
RCR																															
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100													
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91													
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83													
3	99	92	86	81	97	90	85	80	87	83	79	85	81	78	83	79	77	75													
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68													
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62													
6	82	72	65	60	81	71	64	60	69	64	59	68	63	59	67	62	58	57													
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52													
8	73	62	55	50	72	61	55	50	60	54	50	59	54	50	58	53	50	48													
9	69	58	51	47	68	57	51	47	56	50	46	55	50	46	54	50	46	44													
10	65	54	48	43	64	54	47	43	53	47	43	52	47	43	51	46	43	41													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	81949
5°	83284
10°	85858
15°	89302
20°	90585
25°	86283
30°	77453
35°	62486
40°	43116
45°	25677
50°	16248
55°	11079
60°	8620
65°	6986
70°	5632
75°	4392
80°	2637
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25677 cd/sqm



TEST NUMBER: P643170

CATALOG NUMBER: ML5615LSVWFL759FS1E - 594SNB - 1200LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.0	6.4
10°-20°	308.0	19.5
20°-30°	451.0	28.6
30°-40°	398.1	25.2
40°-50°	188.9	12.0
50°-60°	76.1	4.8
60°-70°	37.8	2.4
70°-80°	15.3	1.0
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	860.0	54.5
0°-40°	1258.2	79.7
0°-60°	1523.1	96.5
0°-90°	1577.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1577.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1038	
5°	1051	101
15°	1093	308
25°	991	451
35°	648	398
45°	230	189
55°	80	76
65°	37	38
75°	14	15
85°	0	2
90°	0	



TEST NUMBER: P643170

CATALOG NUMBER: ML5615LSVWFL759FS1E - 594SNB - 1200LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1038.1
2.5°	1042.4
5°	1051.0
7.5°	1061.1
10°	1071.1
12.5°	1082.6
15°	1092.7
17.5°	1094.1
20°	1078.3
22.5°	1042.4
25°	990.6
27.5°	927.4
30°	849.7
32.5°	756.3
35°	648.4
37.5°	530.5
40°	418.4
42.5°	314.9
45°	230.0
47.5°	171.1
50°	132.3
52.5°	102.1
55°	80.5
57.5°	66.1
60°	54.6
62.5°	44.6
65°	37.4
67.5°	31.6
70°	24.4
72.5°	18.7
75°	14.4
77.5°	10.1
80°	5.8
82.5°	2.9
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)