

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643175

Luminaire Tested: ML5615LSVWFL759FS1E - 594SNB - 1500LM - 5000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P643175  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-79)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSVWFL759FS1E - 594SNB - 1500LM - 5000K  
Description: ML56 RR, 75D TIR OPTIC, 5" SATIN NICKLE GIMBAL TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1939.9 lumens  
Efficiency: N/A  
Efficacy: 113.4 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.09  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct

Input Watts (W): 17.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P643175  
CATALOG NUMBER: ML5615LSVWFL759FS1E - 594SNB - 1500LM - 5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P643175

CATALOG NUMBER: ML5615LSVWFL759FS1E - 594SNB - 1500LM - 5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91																											
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83																											
3	99	92	86	81	97	90	85	80	87	83	79	85	81	78	83	79	77	75																											
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68																											
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62																											
6	82	72	65	60	81	71	64	60	69	64	59	68	63	59	67	62	58	57																											
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52																											
8	73	62	55	50	72	61	55	50	60	54	50	59	54	50	58	53	50	48																											
9	69	58	51	47	68	57	51	47	56	50	46	55	50	46	54	50	46	44																											
10	65	54	48	43	64	54	47	43	53	47	43	52	47	43	51	46	43	41																											

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	100744
5°	102389
10°	105561
15°	109790
20°	111368
25°	106081
30°	95228
35°	76825
40°	53009
45°	31572
50°	19969
55°	13625
60°	10610
65°	8592
70°	6924
75°	5399
80°	3228
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 31572 cd/sqm



TEST NUMBER: P643175

CATALOG NUMBER: ML5615LSVWFL759FS1E - 594SNB - 1500LM - 5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	124.1	6.4
10°-20°	378.7	19.5
20°-30°	554.5	28.6
30°-40°	489.5	25.2
40°-50°	232.2	12.0
50°-60°	93.6	4.8
60°-70°	46.5	2.4
70°-80°	18.9	1.0
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1057.3	54.5
0°-40°	1546.8	79.7
0°-60°	1872.6	96.5
0°-90°	1939.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1939.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1276	
5°	1292	124
15°	1343	379
25°	1218	554
35°	797	489
45°	283	232
55°	99	94
65°	46	47
75°	18	19
85°	0	2
90°	0	



TEST NUMBER: P643175

CATALOG NUMBER: ML5615LSVWFL759FS1E - 594SNB - 1500LM - 5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1276.2
2.5°	1281.5
5°	1292.1
7.5°	1304.5
10°	1316.9
12.5°	1331.0
15°	1343.4
17.5°	1345.2
20°	1325.7
22.5°	1281.5
25°	1217.9
27.5°	1140.1
30°	1044.7
32.5°	929.8
35°	797.2
37.5°	652.3
40°	514.4
42.5°	387.1
45°	282.8
47.5°	210.3
50°	162.6
52.5°	125.5
55°	99.0
57.5°	81.3
60°	67.2
62.5°	54.8
65°	46.0
67.5°	38.9
70°	30.0
72.5°	23.0
75°	17.7
77.5°	12.4
80°	7.1
82.5°	3.5
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)