

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643180

Luminaire Tested: ML5615LSVWFL759FS1E - 594SNB - 900LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643180
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-79)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL759FS1E - 594SNB - 900LM - 5000K
Description: ML56 RR, 75D TIR OPTIC, 5" SATIN NICKLE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1247.6 lumens
Efficiency: N/A
Efficacy: 118.8 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.09
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643180

CATALOG NUMBER: ML5615LSVWFL759FS1E - 594SNB - 900LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P643180

CATALOG NUMBER: ML5615LSVWFL759FS1E - 594SNB - 900LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91																												
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83																												
3	99	92	86	81	97	90	85	80	87	83	79	85	81	78	83	79	77	75																												
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68																												
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62																												
6	82	72	65	60	81	71	64	60	69	64	59	68	63	59	67	62	58	57																												
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52																												
8	73	62	55	50	72	61	55	50	60	54	50	59	54	50	58	53	50	48																												
9	69	58	51	47	68	57	51	46	56	50	46	55	50	46	54	50	46	44																												
10	65	54	48	43	64	54	47	43	53	47	43	52	47	43	51	46	43	41																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	64795
5°	65850
10°	67886
15°	70611
20°	71625
25°	68227
30°	61237
35°	49408
40°	34089
45°	20307
50°	12846
55°	8767
60°	6820
65°	5529
70°	4455
75°	3477
80°	2046
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20307 cd/sqm



TEST NUMBER: P643180

CATALOG NUMBER: ML5615LSVWFL759FS1E - 594SNB - 900LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.8	6.4
10°-20°	243.6	19.5
20°-30°	356.6	28.6
30°-40°	314.8	25.2
40°-50°	149.4	12.0
50°-60°	60.2	4.8
60°-70°	29.9	2.4
70°-80°	12.1	1.0
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	680.0	54.5
0°-40°	994.8	79.7
0°-60°	1204.4	96.5
0°-90°	1247.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1247.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	821	
5°	831	80
15°	864	244
25°	783	357
35°	513	315
45°	182	149
55°	64	60
65°	30	30
75°	11	12
85°	0	1
90°	0	



TEST NUMBER: P643180

CATALOG NUMBER: ML5615LSVWFL759FS1E - 594SNB - 900LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	820.8
2.5°	824.2
5°	831.0
7.5°	839.0
10°	846.9
12.5°	856.0
15°	864.0
17.5°	865.1
20°	852.6
22.5°	824.2
25°	783.3
27.5°	733.2
30°	671.8
32.5°	598.0
35°	512.7
37.5°	419.5
40°	330.8
42.5°	249.0
45°	181.9
47.5°	135.3
50°	104.6
52.5°	80.7
55°	63.7
57.5°	52.3
60°	43.2
62.5°	35.2
65°	29.6
67.5°	25.0
70°	19.3
72.5°	14.8
75°	11.4
77.5°	8.0
80°	4.5
82.5°	2.3
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)