

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642834

Luminaire Tested: ML5615LSNFL259FS1E - 594SNB - 900LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642834
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSNFL259FS1E - 594SNB - 900LM - 4000K
Description: ML56 RR, 25D TIR OPTIC, 5" SATIN NICKLE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1242.5 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.43
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642834
CATALOG NUMBER: ML5615LSNFL259FS1E - 594SNB - 900LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P642834

CATALOG NUMBER: ML5615LSNFL259FS1E - 594SNB - 900LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92				
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85				
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	78				
4	96	88	82	78	94	87	81	77	84	80	76	82	78	75	81	77	74	73				
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68				
6	86	77	71	67	85	76	71	66	75	70	66	74	69	66	72	68	65	64				
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60				
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57				
9	75	66	60	56	74	65	59	56	64	59	55	63	59	55	62	58	55	54				
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	55	52	51				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	240778
5°	218820
10°	159476
15°	90397
20°	55579
25°	44953
30°	36789
35°	29576
40°	23434
45°	18398
50°	14381
55°	11272
60°	8968
65°	7229
70°	5239
75°	2776
80°	1546
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18398 cd/sqm



TEST NUMBER: P642834

CATALOG NUMBER: ML5615LSNFL259FS1E - 594SNB - 900LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	238.7	19.2
10°-20°	318.8	25.7
20°-30°	238.0	19.2
30°-40°	192.5	15.5
40°-50°	128.6	10.3
50°-60°	74.6	6.0
60°-70°	39.0	3.1
70°-80°	11.2	0.9
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	795.6	64.0
0°-40°	988.1	79.5
0°-60°	1191.3	95.9
0°-90°	1242.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1242.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3050	
5°	2761	239
15°	1106	319
25°	516	238
35°	307	193
45°	165	129
55°	82	75
65°	39	39
75°	9	11
85°	0	1
90°	0	



TEST NUMBER: P642834

CATALOG NUMBER: ML5615LSNFL259FS1E - 594SNB - 900LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	3050.1
2.5°	2983.1
5°	2761.4
7.5°	2418.0
10°	1989.5
12.5°	1524.5
15°	1106.1
17.5°	819.7
20°	661.6
22.5°	579.8
25°	516.1
27.5°	458.1
30°	403.6
32.5°	352.4
35°	306.9
37.5°	264.9
40°	227.4
42.5°	194.4
45°	164.8
47.5°	138.7
50°	117.1
52.5°	97.8
55°	81.9
57.5°	68.2
60°	56.8
62.5°	47.7
65°	38.7
67.5°	31.8
70°	22.7
72.5°	14.8
75°	9.1
77.5°	5.7
80°	3.4
82.5°	2.3
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)