

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643240

Luminaire Tested: ML5615LSVWFL759FS1E - 691WB - 900LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643240
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-82)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL759FS1E - 691WB - 900LM - 5000K
Description: ML56 RR, 75D TIR OPTIC, 6" DEADFRONT TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1243.0 lumens
Efficiency: N/A
Efficacy: 118.4 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643240

CATALOG NUMBER: ML5615LSVWFL759FS1E - 691WB - 900LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P643240

CATALOG NUMBER: ML5615LSVWFL759FS1E - 691WB - 900LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92																											
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83																											
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																											
4	94	85	79	74	92	84	78	73	82	76	72	79	75	72	78	74	71	69																											
5	88	78	72	67	86	77	71	67	76	70	66	74	69	65	72	68	65	63																											
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58																											
7	78	67	61	56	76	67	60	56	65	59	55	64	59	55	63	58	55	53																											
8	73	63	56	51	72	62	56	51	61	55	51	60	55	51	59	54	50	49																											
9	69	58	52	47	68	58	52	47	57	51	47	56	51	47	55	50	47	45																											
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	45764
5°	46439
10°	47990
15°	49898
20°	50428
25°	47743
30°	42912
35°	34706
40°	24095
45°	14459
50°	9219
55°	5763
60°	3870
65°	2504
70°	1282
75°	720
80°	726
85°	692

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14459 cd/sqm



TEST NUMBER: P643240

CATALOG NUMBER: ML5615LSVWFL759FS1E - 691WB - 900LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.2	6.5
10°-20°	247.5	19.9
20°-30°	359.9	29.0
30°-40°	318.7	25.6
40°-50°	153.2	12.3
50°-60°	57.1	4.6
60°-70°	19.6	1.6
70°-80°	4.3	0.3
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	688.6	55.4
0°-40°	1007.3	81.0
0°-60°	1217.5	98.0
0°-90°	1243.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1243.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	835	
5°	844	81
15°	879	248
25°	789	360
35°	519	319
45°	186	153
55°	60	57
65°	19	20
75°	3	4
85°	1	2
90°	0	



TEST NUMBER: P643240

CATALOG NUMBER: ML5615LSVWFL759FS1E - 691WB - 900LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	834.8
2.5°	837.1
5°	843.9
7.5°	853.0
10°	862.1
12.5°	871.2
15°	879.2
17.5°	878.0
20°	864.4
22.5°	832.6
25°	789.3
27.5°	739.3
30°	677.9
32.5°	603.9
35°	518.6
37.5°	426.5
40°	336.7
42.5°	253.6
45°	186.5
47.5°	141.0
50°	108.1
52.5°	79.6
55°	60.3
57.5°	45.5
60°	35.3
62.5°	27.3
65°	19.3
67.5°	11.4
70°	8.0
72.5°	4.5
75°	3.4
77.5°	3.4
80°	2.3
82.5°	2.3
85°	1.1
87.5°	1.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)