

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642835

Luminaire Tested: ML5615LSNFL259FS1E - 594SNB - 900LM - 5000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642835  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSNFL259FS1E - 594SNB - 900LM - 5000K  
Description: ML56 RR, 25D TIR OPTIC, 5" SATIN NICKLE GIMBAL TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1243.0 lumens  
Efficiency: N/A  
Efficacy: 118.4 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.43  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642835  
CATALOG NUMBER: ML5615LSNFL259FS1E - 594SNB - 900LM - 5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P642835

CATALOG NUMBER: ML5615LSNFL259FS1E - 594SNB - 900LM - 5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			92
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	78			78
4	96	88	82	78	94	87	81	77	84	80	76	82	78	75	81	77	74	73			73
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68			68
6	86	77	71	67	85	76	71	66	75	70	66	74	69	66	72	68	65	64			64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60			60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57			57
9	75	66	60	56	74	65	59	56	64	59	55	63	59	55	62	58	55	54			54
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	55	52	51			51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	240872
5°	218899
10°	159532
15°	90438
20°	55604
25°	44971
30°	36799
35°	29595
40°	23444
45°	18409
50°	14381
55°	11272
60°	8983
65°	7229
70°	5239
75°	2776
80°	1546
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18409 cd/sqm



TEST NUMBER: P642835

CATALOG NUMBER: ML5615LSNFL259FS1E - 594SNB - 900LM - 5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	238.8	19.2
10°-20°	318.9	25.7
20°-30°	238.1	19.2
30°-40°	192.6	15.5
40°-50°	128.6	10.3
50°-60°	74.6	6.0
60°-70°	39.0	3.1
70°-80°	11.2	0.9
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	795.9	64.0
0°-40°	988.5	79.5
0°-60°	1191.7	95.9
0°-90°	1243.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1243.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3051	
5°	2762	239
15°	1107	319
25°	516	238
35°	307	193
45°	165	129
55°	82	75
65°	39	39
75°	9	11
85°	0	1
90°	0	



TEST NUMBER: P642835

CATALOG NUMBER: ML5615LSNFL259FS1E - 594SNB - 900LM - 5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3051.3
2.5°	2984.2
5°	2762.4
7.5°	2419.0
10°	1990.2
12.5°	1525.1
15°	1106.6
17.5°	820.0
20°	661.9
22.5°	580.0
25°	516.3
27.5°	458.3
30°	403.7
32.5°	352.6
35°	307.1
37.5°	265.0
40°	227.5
42.5°	194.5
45°	164.9
47.5°	138.7
50°	117.1
52.5°	97.8
55°	81.9
57.5°	68.2
60°	56.9
62.5°	47.8
65°	38.7
67.5°	31.8
70°	22.7
72.5°	14.8
75°	9.1
77.5°	5.7
80°	3.4
82.5°	2.3
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)