

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642843

Luminaire Tested: ML5615LSNFL259FS1E - 594TBZB - 1500LM - 3500K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642843  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSNFL259FS1E - 594TBZB - 1500LM - 3500K  
Description: ML56 RR, 25D TIR OPTIC, 5" TUSCON BRONZE GIMBAL TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1797.3 lumens  
Efficiency: N/A  
Efficacy: 105.1 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.43  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct


Input Watts (W): 17.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642843

CATALOG NUMBER: ML5615LSNFL259FS1E - 594TBZB - 1500LM - 3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P642843

CATALOG NUMBER: ML5615LSNFL259FS1E - 594TBZB - 1500LM - 3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92																			
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85																			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	78																			
4	96	88	82	77	94	87	81	77	84	80	76	82	78	75	81	77	74	73																			
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68																			
6	86	77	71	67	85	76	71	66	75	70	66	73	69	65	72	68	65	64																			
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	66	60	56	74	65	59	56	64	59	55	63	59	55	62	58	55	54																			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	347466
5°	316130
10°	230657
15°	130867
20°	80437
25°	64952
30°	52996
35°	42730
40°	33852
45°	26581
50°	20779
55°	16282
60°	12962
65°	10740
70°	7570
75°	3996
80°	3000
85°	1449

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 26581 cd/sqm



TEST NUMBER: P642843

CATALOG NUMBER: ML5615LSNFL259FS1E - 594TBZB - 1500LM - 3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	344.5	19.2
10°-20°	461.4	25.7
20°-30°	343.9	19.1
30°-40°	278.3	15.5
40°-50°	186.1	10.4
50°-60°	107.7	6.0
60°-70°	56.8	3.2
70°-80°	16.4	0.9
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1149.8	64.0
0°-40°	1428.1	79.5
0°-60°	1721.9	95.8
0°-90°	1797.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1797.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4402	
5°	3989	344
15°	1601	461
25°	746	344
35°	443	278
45°	238	186
55°	118	108
65°	58	57
75°	13	16
85°	2	2
90°	0	



TEST NUMBER: P642843

CATALOG NUMBER: ML5615LSNFL259FS1E - 594TBZB - 1500LM - 3500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4401.6
2.5°	4304.7
5°	3989.4
7.5°	3481.9
10°	2877.5
12.5°	2205.7
15°	1601.3
17.5°	1187.5
20°	957.5
22.5°	837.6
25°	745.7
27.5°	661.9
30°	581.4
32.5°	510.8
35°	443.4
37.5°	382.7
40°	328.5
42.5°	280.9
45°	238.1
47.5°	202.0
50°	169.2
52.5°	141.2
55°	118.3
57.5°	98.5
60°	82.1
62.5°	69.0
65°	57.5
67.5°	46.0
70°	32.8
72.5°	21.4
75°	13.1
77.5°	8.2
80°	6.6
82.5°	3.3
85°	1.6
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)