

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642850

Luminaire Tested: ML5615LSNFL259FS1E - 594TBZB - 900LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642850
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSNFL259FS1E - 594TBZB - 900LM - 5000K
Description: ML56 RR, 25D TIR OPTIC, 5" TUSCON BRONZE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1244.2 lumens
Efficiency: N/A
Efficacy: 118.5 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.43
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642850
CATALOG NUMBER: ML5615LSNFL259FS1E - 594TBZB - 900LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P642850
 CATALOG NUMBER: ML5615LSNFL259FS1E - 594TBZB - 900LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92																			
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85																			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	78																			
4	96	88	82	77	94	87	81	77	84	80	76	82	78	75	81	77	74	73																			
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68																			
6	86	77	71	67	85	76	71	66	75	70	66	73	69	65	72	68	65	64																			
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	66	60	56	74	65	59	56	64	59	55	63	59	55	62	58	55	54																			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	240533
5°	218836
10°	159668
15°	90593
20°	55680
25°	44962
30°	36689
35°	29585
40°	23434
45°	18409
50°	14381
55°	11272
60°	8968
65°	7434
70°	5239
75°	2776
80°	2046
85°	996

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18409 cd/sqm



TEST NUMBER: P642850

CATALOG NUMBER: ML5615LSNFL259FS1E - 594TBZB - 900LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	238.5	19.2
10°-20°	319.4	25.7
20°-30°	238.0	19.1
30°-40°	192.7	15.5
40°-50°	128.8	10.4
50°-60°	74.6	6.0
60°-70°	39.3	3.2
70°-80°	11.4	0.9
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	795.9	64.0
0°-40°	988.6	79.5
0°-60°	1192.0	95.8
0°-90°	1244.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1244.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3047	
5°	2762	238
15°	1108	319
25°	516	238
35°	307	193
45°	165	129
55°	82	75
65°	40	39
75°	9	11
85°	1	2
90°	0	



TEST NUMBER: P642850
CATALOG NUMBER: ML5615LSNFL259FS1E - 594TBZB - 900LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	3047.0
2.5°	2979.9
5°	2761.6
7.5°	2410.3
10°	1991.9
12.5°	1526.9
15°	1108.5
17.5°	822.0
20°	662.8
22.5°	579.8
25°	516.2
27.5°	458.2
30°	402.5
32.5°	353.6
35°	307.0
37.5°	264.9
40°	227.4
42.5°	194.4
45°	164.9
47.5°	139.8
50°	117.1
52.5°	97.8
55°	81.9
57.5°	68.2
60°	56.8
62.5°	47.8
65°	39.8
67.5°	31.8
70°	22.7
72.5°	14.8
75°	9.1
77.5°	5.7
80°	4.5
82.5°	2.3
85°	1.1
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)