

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643293

Luminaire Tested: ML5615LSVWFL759FS1E - 693BB - 1500LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643293
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-87)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL759FS1E - 693BB - 1500LM - 3500K
Description: ML56 RR, 75D TIR OPTIC, 6" BLACK BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1726.7 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643293

CATALOG NUMBER: ML5615LSVWFL759FS1E - 693BB - 1500LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P643293

CATALOG NUMBER: ML5615LSVWFL759FS1E - 693BB - 1500LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92																																				
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84																																				
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77																																				
4	95	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	71																																				
5	89	80	73	68	87	79	73	68	77	72	67	75	70	67	73	69	66	65																																				
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59																																				
7	79	69	62	57	78	68	62	57	67	61	57	65	60	56	64	60	56	55																																				
8	75	64	57	53	73	63	57	53	62	56	52	61	56	52	60	55	52	50																																				
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47																																				
10	67	56	50	45	66	55	49	45	55	49	45	54	49	45	53	48	45	43																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	66206
5°	67274
10°	69426
15°	72089
20°	72853
25°	69077
30°	61788
35°	49597
40°	33749
45°	19490
50°	10652
55°	6442
60°	3245
65°	856
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19490 cd/sqm



TEST NUMBER: P643293

CATALOG NUMBER: ML5615LSVWFL759FS1E - 693BB - 1500LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.5	6.8
10°-20°	357.8	20.7
20°-30°	520.2	30.1
30°-40°	454.5	26.3
40°-50°	204.9	11.9
50°-60°	62.6	3.6
60°-70°	9.2	0.5
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	995.5	57.7
0°-40°	1450.0	84.0
0°-60°	1717.5	99.5
0°-90°	1726.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1726.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1208	
5°	1222	118
15°	1270	358
25°	1142	520
35°	741	455
45°	251	205
55°	67	63
65°	7	9
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P643293

CATALOG NUMBER: ML5615LSVWFL759FS1E - 693BB - 1500LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1207.7
2.5°	1212.7
5°	1222.5
7.5°	1235.7
10°	1247.2
12.5°	1260.3
15°	1270.2
17.5°	1268.5
20°	1248.8
22.5°	1204.5
25°	1142.0
27.5°	1068.1
30°	976.1
32.5°	864.3
35°	741.1
37.5°	604.7
40°	471.6
42.5°	350.0
45°	251.4
47.5°	177.5
50°	124.9
52.5°	90.4
55°	67.4
57.5°	47.7
60°	29.6
62.5°	14.8
65°	6.6
67.5°	1.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)