

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642891

Luminaire Tested: ML5615LSNFL259FS1E - 691WB - 900LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642891
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSNFL259FS1E - 691WB - 900LM - 2700K
Description: ML56 RR, 25D TIR OPTIC, 6" DEADFRONT TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1085.0 lumens
Efficiency: N/A
Efficacy: 103.3 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642891

CATALOG NUMBER: ML5615LSNFL259FS1E - 691WB - 900LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P642891

CATALOG NUMBER: ML5615LSNFL259FS1E - 691WB - 900LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	91	94	92	90	92	89	88	86																			
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	86	84	81	80																			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74																			
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69																			
6	87	78	72	68	86	78	72	68	76	71	67	75	70	67	73	69	66	65																			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61																			
8	80	70	64	60	78	70	64	60	68	63	60	67	63	59	66	62	59	58																			
9	76	67	61	57	75	66	61	57	65	60	57	64	60	56	63	59	56	55																			
10	73	63	58	54	72	63	58	54	62	57	54	61	57	54	61	57	53	52																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	147181
5°	134707
10°	98133
15°	56408
20°	34536
25°	27945
30°	22915
35°	18672
40°	15028
45°	12017
50°	9467
55°	6117
60°	2412
65°	1816
70°	1443
75°	1271
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12017 cd/sqm



TEST NUMBER: P642891

CATALOG NUMBER: ML5615LSNFL259FS1E - 691WB - 900LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	211.1	19.5
10°-20°	285.0	26.3
20°-30°	212.9	19.6
30°-40°	175.0	16.1
40°-50°	120.6	11.1
50°-60°	57.9	5.3
60°-70°	13.9	1.3
70°-80°	6.5	0.6
80°-90°	2.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	709.0	65.3
0°-40°	884.0	81.5
0°-60°	1062.5	97.9
0°-90°	1085.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1085.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2685	
5°	2448	211
15°	994	285
25°	462	213
35°	279	175
45°	155	121
55°	64	58
65°	14	14
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P642891

CATALOG NUMBER: ML5615LSNFL259FS1E - 691WB - 900LM - 2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2684.8
2.5°	2630.8
5°	2447.9
7.5°	2134.9
10°	1762.9
12.5°	1358.9
15°	993.9
17.5°	736.0
20°	592.0
22.5°	517.0
25°	462.0
27.5°	410.0
30°	362.0
32.5°	318.0
35°	279.0
37.5°	243.0
40°	210.0
42.5°	181.0
45°	155.0
47.5°	132.0
50°	111.0
52.5°	90.0
55°	64.0
57.5°	41.0
60°	22.0
62.5°	16.0
65°	14.0
67.5°	11.0
70°	9.0
72.5°	7.0
75°	6.0
77.5°	5.0
80°	4.0
82.5°	3.0
85°	2.0
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)