

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642908

Luminaire Tested: ML5615LSNFL259FS1E - 692H - 900LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642908
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSNFL259FS1E - 692H - 900LM - 3500K
Description: ML56 RR, 25D TIR OPTIC, 6" HAZE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1121.1 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642908
CATALOG NUMBER: ML5615LSNFL259FS1E - 692H - 900LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P642908

CATALOG NUMBER: ML5615LSNFL259FS1E - 692H - 900LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																			
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82																			
4	98	91	86	82	96	90	85	81	88	83	80	86	82	79	84	81	78	77																			
5	94	86	80	76	92	85	79	76	83	78	75	81	77	74	80	76	74	72																			
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	69	68																			
7	85	77	71	67	84	76	70	67	75	70	66	73	69	66	72	69	66	64																			
8	82	73	67	63	81	72	67	63	71	66	63	70	66	62	69	65	62	61																			
9	78	69	64	60	77	69	63	60	68	63	60	67	63	59	66	62	59	58																			
10	75	66	61	57	74	66	60	57	65	60	57	64	60	57	63	59	56	55																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	160365
5°	146263
10°	107480
15°	62140
20°	38597
25°	31006
30°	25352
35°	20512
40°	16187
45°	12211
50°	6311
55°	1816
60°	1162
65°	687
70°	337
75°	233
80°	347
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12211 cd/sqm



TEST NUMBER: P642908

CATALOG NUMBER: ML5615LSNFL259FS1E - 692H - 900LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	230.1	20.5
10°-20°	314.2	28.0
20°-30°	236.6	21.1
30°-40°	192.1	17.1
40°-50°	117.3	10.5
50°-60°	24.2	2.2
60°-70°	5.2	0.5
70°-80°	1.3	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	780.9	69.7
0°-40°	973.0	86.8
0°-60°	1114.4	99.4
0°-90°	1121.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1121.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2925	
5°	2658	230
15°	1095	314
25°	513	237
35°	306	192
45°	158	117
55°	19	24
65°	5	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P642908

CATALOG NUMBER: ML5615LSNFL259FS1E - 692H - 900LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2925.3
2.5°	2863.0
5°	2657.9
7.5°	2330.3
10°	1930.8
12.5°	1487.0
15°	1094.9
17.5°	820.1
20°	661.6
22.5°	576.0
25°	512.6
27.5°	454.4
30°	400.5
32.5°	353.0
35°	306.5
37.5°	264.2
40°	226.2
42.5°	192.3
45°	157.5
47.5°	114.1
50°	74.0
52.5°	34.9
55°	19.0
57.5°	13.7
60°	10.6
62.5°	7.4
65°	5.3
67.5°	2.1
70°	2.1
72.5°	1.1
75°	1.1
77.5°	1.1
80°	1.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)