

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643300

Luminaire Tested: ML5615LSVWFL759FS1E - 693BB - 900LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643300
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-87)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL759FS1E - 693BB - 900LM - 5000K
Description: ML56 RR, 75D TIR OPTIC, 6" BLACK BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1195.2 lumens
Efficiency: N/A
Efficacy: 113.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643300
CATALOG NUMBER: ML5615LSVWFL759FS1E - 693BB - 900LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P643300

CATALOG NUMBER: ML5615LSVWFL759FS1E - 693BB - 900LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92				92															
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84				84															
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77				77															
4	95	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	71				71															
5	89	80	73	68	87	79	73	68	77	72	67	75	70	67	73	69	66	65				65															
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59				59															
7	79	69	62	57	78	68	62	57	67	61	57	65	60	56	64	60	56	55				55															
8	75	64	57	53	73	63	57	53	62	56	52	61	56	52	60	55	52	50				50															
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47				47															
10	67	56	50	45	66	55	49	45	55	49	45	54	49	45	53	48	45	43				43															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	45830
5°	46572
10°	48056
15°	49904
20°	50434
25°	47815
30°	42772
35°	34332
40°	23365
45°	13490
50°	7369
55°	4454
60°	2248
65°	584
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13490 cd/sqm



TEST NUMBER: P643300

CATALOG NUMBER: ML5615LSVWFL759FS1E - 693BB - 900LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.4	6.8
10°-20°	247.7	20.7
20°-30°	360.1	30.1
30°-40°	314.6	26.3
40°-50°	141.8	11.9
50°-60°	43.3	3.6
60°-70°	6.3	0.5
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	689.1	57.7
0°-40°	1003.7	84.0
0°-60°	1188.9	99.5
0°-90°	1195.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1195.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	836	
5°	846	81
15°	879	248
25°	790	360
35°	513	315
45°	174	142
55°	47	43
65°	4	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P643300

CATALOG NUMBER: ML5615LSVWFL759FS1E - 693BB - 900LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	836.0
2.5°	839.5
5°	846.3
7.5°	855.4
10°	863.3
12.5°	872.4
15°	879.3
17.5°	878.1
20°	864.5
22.5°	833.8
25°	790.5
27.5°	739.4
30°	675.7
32.5°	598.3
35°	513.0
37.5°	418.6
40°	326.5
42.5°	242.3
45°	174.0
47.5°	122.8
50°	86.4
52.5°	62.6
55°	46.6
57.5°	33.0
60°	20.5
62.5°	10.2
65°	4.5
67.5°	1.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)