

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642918

Luminaire Tested: ML5615LSNFL259FS1E - 692SC - 1500LM - 3500K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642918  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSNFL259FS1E - 692SC - 1500LM - 3500K  
Description: ML56 RR, 25D TIR OPTIC, 6" SPECULAR CLEAR TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1772.6 lumens  
Efficiency: N/A  
Efficacy: 103.7 lumens/watt  
Spacing Criteria (0/90/45): 0.37 / 0.37 / 0.39  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 17.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642918  
CATALOG NUMBER: ML5615LSNFL259FS1E - 692SC - 1500LM - 3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P642918

CATALOG NUMBER: ML5615LSNFL259FS1E - 692SC - 1500LM - 3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	89				89
3	104	98	93	89	102	96	92	89	94	90	87	91	89	86	89	87	85	83				83
4	99	92	87	83	97	91	86	83	89	85	82	87	83	81	85	82	80	78				78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74				74
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70				70
7	87	78	73	69	85	78	72	69	76	72	68	75	71	68	74	70	68	66				66
8	83	75	69	65	82	74	69	65	73	68	65	72	68	65	71	67	64	63				63
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	60				60
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	58				58

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	319152
5°	276865
10°	180151
15°	97759
20°	58683
25°	46527
30°	37873
35°	30356
40°	23880
45°	18219
50°	9390
55°	2198
60°	1261
65°	636
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18219 cd/sqm



TEST NUMBER: P642918

CATALOG NUMBER: ML5615LSNFL259FS1E - 692SC - 1500LM - 3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	420.3	23.7
10°-20°	500.2	28.2
20°-30°	355.8	20.1
30°-40°	285.0	16.1
40°-50°	173.9	9.8
50°-60°	32.4	1.8
60°-70°	5.0	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1276.3	72.0
0°-40°	1561.3	88.1
0°-60°	1767.6	99.7
0°-90°	1772.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1772.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5822	
5°	5031	420
15°	1722	500
25°	769	356
35°	454	285
45°	235	174
55°	23	32
65°	5	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P642918

CATALOG NUMBER: ML5615LSNFL259FS1E - 692SC - 1500LM - 3500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5821.8
2.5°	5647.6
5°	5031.2
7.5°	4130.5
10°	3236.3
12.5°	2407.9
15°	1722.5
17.5°	1265.6
20°	1005.9
22.5°	869.5
25°	769.2
27.5°	680.5
30°	598.3
32.5°	524.3
35°	453.6
37.5°	391.2
40°	333.7
42.5°	284.3
45°	235.0
47.5°	169.3
50°	110.1
52.5°	49.3
55°	23.0
57.5°	14.8
60°	11.5
62.5°	8.2
65°	4.9
67.5°	1.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)