

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643316

Luminaire Tested: ML5615LSVWFL759FS1E - 693TBZB - 1200LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643316
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-89)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL759FS1E - 693TBZB - 1200LM - 2700K
Description: ML56 RR, 75D TIR OPTIC, 6" TUSCON BRONZE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1338.2 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643316

CATALOG NUMBER: ML5615LSVWFL759FS1E - 693TBZB - 1200LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P643316

CATALOG NUMBER: ML5615LSVWFL759FS1E - 693TBZB - 1200LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20										
RC	80					70					50					30					10					0					
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0				
RCR																															
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100													
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92													
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84													
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77													
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70													
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65													
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59													
7	79	69	62	57	77	68	62	57	67	61	57	65	60	56	64	60	56	55													
8	74	64	57	53	73	63	57	53	62	56	52	61	56	52	60	55	52	50													
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47													
10	67	56	49	45	66	55	49	45	55	49	45	54	49	45	53	48	45	43													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51213
5°	52108
10°	53695
15°	55755
20°	56273
25°	53368
30°	47761
35°	38293
40°	26185
45°	15211
50°	8418
55°	5085
60°	2642
65°	662
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15211 cd/sqm



TEST NUMBER: P643316

CATALOG NUMBER: ML5615LSVWFL759FS1E - 693TBZB - 1200LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.9	6.8
10°-20°	276.6	20.7
20°-30°	401.9	30.0
30°-40°	352.2	26.3
40°-50°	159.8	11.9
50°-60°	49.5	3.7
60°-70°	7.3	0.5
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	769.4	57.5
0°-40°	1121.6	83.8
0°-60°	1330.9	99.5
0°-90°	1338.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1338.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	934	
5°	947	91
15°	982	277
25°	882	402
35°	572	352
45°	196	160
55°	53	50
65°	5	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P643316

CATALOG NUMBER: ML5615LSVWFL759FS1E - 693TBZB - 1200LM - 2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	934.2
2.5°	939.3
5°	946.9
7.5°	955.8
10°	964.6
12.5°	973.5
15°	982.4
17.5°	981.1
20°	964.6
22.5°	930.4
25°	882.3
27.5°	825.4
30°	754.5
32.5°	670.9
35°	572.2
37.5°	469.7
40°	365.9
42.5°	272.2
45°	196.2
47.5°	139.3
50°	98.7
52.5°	70.9
55°	53.2
57.5°	38.0
60°	24.1
62.5°	11.4
65°	5.1
67.5°	1.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)