

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643354

Luminaire Tested: ML5615LSVWFL759FS1E - 694TBZB - 1500LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643354
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-91)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL759FS1E - 694TBZB - 1500LM - 4000K
Description: ML56 RR, 75D TIR OPTIC, 6" TUSCON BRONZE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1940.9 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643354

CATALOG NUMBER: ML5615LSVWFL759FS1E - 694TBZB - 1500LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P643354

CATALOG NUMBER: ML5615LSVWFL759FS1E - 694TBZB - 1500LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68			
5	88	78	71	66	86	77	71	66	75	69	65	73	68	65	72	67	64	62			
6	82	72	65	60	81	71	65	60	70	64	60	68	63	59	67	62	59	57			
7	78	67	60	55	76	66	60	55	65	59	55	64	58	54	62	58	54	52			
8	73	62	55	51	72	62	55	51	61	55	50	59	54	50	58	54	50	48			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			
10	65	54	48	44	64	54	48	43	53	47	43	52	47	43	51	47	43	42			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71184
5°	72430
10°	75038
15°	78207
20°	78739
25°	74266
30°	65871
35°	52374
40°	35903
45°	21227
50°	13560
55°	9452
60°	7170
65°	5954
70°	4809
75°	3749
80°	2241
85°	1132

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 21227 cd/sqm



TEST NUMBER: P643354

CATALOG NUMBER: ML5615LSVWFL759FS1E - 694TBZB - 1500LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.6	6.5
10°-20°	387.6	20.0
20°-30°	558.7	28.8
30°-40°	482.0	24.8
40°-50°	225.9	11.6
50°-60°	92.6	4.8
60°-70°	46.3	2.4
70°-80°	18.9	1.0
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1072.9	55.3
0°-40°	1554.9	80.1
0°-60°	1873.4	96.5
0°-90°	1940.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1940.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1298	
5°	1316	127
15°	1378	388
25°	1228	559
35°	783	482
45°	274	226
55°	99	93
65°	46	46
75°	18	19
85°	2	2
90°	0	



TEST NUMBER: P643354

CATALOG NUMBER: ML5615LSVWFL759FS1E - 694TBZB - 1500LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1298.5
2.5°	1303.8
5°	1316.2
7.5°	1330.3
10°	1348.0
12.5°	1363.9
15°	1378.0
17.5°	1376.2
20°	1349.7
22.5°	1298.5
25°	1227.8
27.5°	1143.0
30°	1040.6
32.5°	918.7
35°	782.6
37.5°	639.5
40°	501.7
42.5°	374.5
45°	273.8
47.5°	206.7
50°	159.0
52.5°	123.7
55°	98.9
57.5°	81.3
60°	65.4
62.5°	54.8
65°	45.9
67.5°	38.9
70°	30.0
72.5°	23.0
75°	17.7
77.5°	12.4
80°	7.1
82.5°	3.5
85°	1.8
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)