

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643359

Luminaire Tested: ML5615LSVWFL759FS1E - 694TBZB - 900LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643359
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-91)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL759FS1E - 694TBZB - 900LM - 4000K
Description: ML56 RR, 75D TIR OPTIC, 6" TUSCON BRONZE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1248.2 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643359

CATALOG NUMBER: ML5615LSVWFL759FS1E - 694TBZB - 900LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P643359

CATALOG NUMBER: ML5615LSVWFL759FS1E - 694TBZB - 900LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75																			
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68																			
5	88	78	71	66	86	77	71	66	75	69	65	73	68	65	72	67	64	62																			
6	82	72	65	60	81	71	65	60	70	64	60	68	63	59	67	62	59	57																			
7	78	67	60	55	76	66	60	55	65	59	55	64	58	54	62	58	54	52																			
8	73	62	55	51	72	62	55	51	61	55	50	59	54	50	58	54	50	48																			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45																			
10	65	54	48	44	64	54	48	43	53	47	43	52	47	43	51	47	43	42																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	45780
5°	46583
10°	48257
15°	50295
20°	50638
25°	47767
30°	42361
35°	33682
40°	23093
45°	13653
50°	8725
55°	6079
60°	4605
65°	3827
70°	3093
75°	2415
80°	1421
85°	692

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13653 cd/sqm



TEST NUMBER: P643359

CATALOG NUMBER: ML5615LSVWFL759FS1E - 694TBZB - 900LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.4	6.5
10°-20°	249.3	20.0
20°-30°	359.3	28.8
30°-40°	310.0	24.8
40°-50°	145.3	11.6
50°-60°	59.5	4.8
60°-70°	29.7	2.4
70°-80°	12.1	1.0
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	690.0	55.3
0°-40°	1000.0	80.1
0°-60°	1204.8	96.5
0°-90°	1248.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1248.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	835	
5°	846	81
15°	886	249
25°	790	359
35°	503	310
45°	176	145
55°	64	60
65°	30	30
75°	11	12
85°	1	2
90°	0	



TEST NUMBER: P643359

CATALOG NUMBER: ML5615LSVWFL759FS1E - 694TBZB - 900LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	835.1
2.5°	838.5
5°	846.5
7.5°	855.5
10°	866.9
12.5°	877.1
15°	886.2
17.5°	885.1
20°	868.0
22.5°	835.1
25°	789.7
27.5°	735.1
30°	669.2
32.5°	590.8
35°	503.3
37.5°	411.3
40°	322.7
42.5°	240.9
45°	176.1
47.5°	132.9
50°	102.3
52.5°	79.5
55°	63.6
57.5°	52.3
60°	42.0
62.5°	35.2
65°	29.5
67.5°	25.0
70°	19.3
72.5°	14.8
75°	11.4
77.5°	8.0
80°	4.5
82.5°	2.3
85°	1.1
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)