

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643391

Luminaire Tested: ML5615LSVWFL9FS1E - 591WB - 1200LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643391
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-93)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL9FS1E - 591WB - 1200LM - 2700K
Description: ML56 RR, MILKY OPTIC, 5" DEADFRONT TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1291.3 lumens
Efficiency: N/A
Efficacy: 96.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643391
CATALOG NUMBER: ML5615LSVWFL9FS1E - 591WB - 1200LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P643391

CATALOG NUMBER: ML5615LSVWFL9FS1E - 591WB - 1200LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77																			
3	95	87	80	74	93	85	79	74	82	77	73	80	75	71	77	73	70	68																			
4	89	78	71	65	87	77	70	65	75	69	64	73	67	63	71	66	62	61																			
5	82	71	64	58	81	70	63	58	68	62	57	66	61	56	65	60	56	54																			
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49																			
7	72	60	52	47	70	59	52	46	58	51	46	56	50	46	55	50	46	44																			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40																			
9	63	51	44	39	62	50	43	38	49	43	38	48	42	38	47	42	38	36																			
10	59	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53585
5°	53489
10°	53193
15°	52787
20°	52143
25°	51198
30°	49888
35°	47510
40°	42601
45°	34005
50°	24992
55°	18263
60°	13973
65°	11562
70°	10502
75°	10401
80°	10910
85°	11412

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 34005 cd/sqm



TEST NUMBER: P643391

CATALOG NUMBER: ML5615LSVWFL9FS1E - 591WB - 1200LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.1	5.0
10°-20°	181.9	14.1
20°-30°	270.5	20.9
30°-40°	305.1	23.6
40°-50°	234.6	18.2
50°-60°	122.2	9.5
60°-70°	63.1	4.9
70°-80°	36.2	2.8
80°-90°	13.6	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	516.5	40.0
0°-40°	821.6	63.6
0°-60°	1178.4	91.3
0°-90°	1291.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1291.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	679	
5°	675	64
15°	646	182
25°	588	270
35°	493	305
45°	305	235
55°	133	122
65°	62	63
75°	34	36
85°	13	14
90°	0	



TEST NUMBER: P643391

CATALOG NUMBER: ML5615LSVWFL9FS1E - 591WB - 1200LM - 2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	678.8
2.5°	677.5
5°	675.0
7.5°	670.0
10°	663.6
12.5°	654.8
15°	645.9
17.5°	633.3
20°	620.7
22.5°	605.5
25°	587.8
27.5°	568.8
30°	547.3
32.5°	522.1
35°	493.0
37.5°	457.6
40°	413.4
42.5°	361.5
45°	304.6
47.5°	249.0
50°	203.5
52.5°	163.1
55°	132.7
57.5°	107.4
60°	88.5
62.5°	73.3
65°	61.9
67.5°	53.1
70°	45.5
72.5°	39.2
75°	34.1
77.5°	29.1
80°	24.0
82.5°	19.0
85°	12.6
87.5°	6.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)