

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643402

Luminaire Tested: ML5615LSVWFL9FS1E - 591WB - 900LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643402
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-93)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL9FS1E - 591WB - 900LM - 3000K
Description: ML56 RR, MILKY OPTIC, 5" DEADFRONT TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1050.2 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643402

CATALOG NUMBER: ML5615LSVWFL9FS1E - 591WB - 900LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P643402

CATALOG NUMBER: ML5615LSVWFL9FS1E - 591WB - 900LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77																			
3	95	87	80	74	93	85	79	74	82	77	73	80	75	71	77	73	70	68																			
4	89	78	71	65	87	77	70	65	75	69	64	73	67	63	71	66	62	61																			
5	82	71	64	58	81	70	63	58	68	62	57	66	61	56	65	60	56	54																			
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49																			
7	72	60	52	47	70	59	52	46	58	51	46	56	50	46	55	50	46	44																			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40																			
9	63	51	44	39	62	50	43	38	49	43	38	48	42	38	47	42	38	36																			
10	59	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43575
5°	43504
10°	43262
15°	42930
20°	42407
25°	41635
30°	40572
35°	38634
40°	34645
45°	27664
50°	20325
55°	14850
60°	11367
65°	9414
70°	8540
75°	8479
80°	8865
85°	9329

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 27664 cd/sqm



TEST NUMBER: P643402

CATALOG NUMBER: ML5615LSVWFL9FS1E - 591WB - 900LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.1	5.0
10°-20°	148.0	14.1
20°-30°	220.0	20.9
30°-40°	248.1	23.6
40°-50°	190.8	18.2
50°-60°	99.4	9.5
60°-70°	51.3	4.9
70°-80°	29.4	2.8
80°-90°	11.0	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	420.0	40.0
0°-40°	668.2	63.6
0°-60°	958.4	91.3
0°-90°	1050.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1050.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	552	
5°	549	52
15°	525	148
25°	478	220
35°	401	248
45°	248	191
55°	108	99
65°	50	51
75°	28	29
85°	10	11
90°	0	



TEST NUMBER: P643402

CATALOG NUMBER: ML5615LSVWFL9FS1E - 591WB - 900LM - 3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	552.0
2.5°	551.0
5°	549.0
7.5°	544.8
10°	539.7
12.5°	532.5
15°	525.3
17.5°	515.0
20°	504.8
22.5°	492.4
25°	478.0
27.5°	462.6
30°	445.1
32.5°	424.6
35°	400.9
37.5°	372.1
40°	336.2
42.5°	294.0
45°	247.8
47.5°	202.5
50°	165.5
52.5°	132.6
55°	107.9
57.5°	87.4
60°	72.0
62.5°	59.6
65°	50.4
67.5°	43.2
70°	37.0
72.5°	31.9
75°	27.8
77.5°	23.6
80°	19.5
82.5°	15.4
85°	10.3
87.5°	5.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)