

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642950

Luminaire Tested: ML5615LSNFL259FS1E - 693BB - 1500LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642950
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSNFL259FS1E - 693BB - 1500LM - 5000K
Description: ML56 RR, 25D TIR OPTIC, 6" BLACK BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1765.7 lumens
Efficiency: N/A
Efficacy: 103.3 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.43
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642950
CATALOG NUMBER: ML5615LSNFL259FS1E - 693BB - 1500LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P642950

CATALOG NUMBER: ML5615LSNFL259FS1E - 693BB - 1500LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																												
2	108	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88																												
3	103	97	92	89	101	96	92	88	93	90	87	91	88	85	89	86	84	82																												
4	98	91	86	82	97	90	85	82	88	84	81	86	83	80	84	81	79	77																												
5	94	86	81	76	92	85	80	76	83	79	75	82	78	75	80	77	74	73																												
6	90	81	76	72	88	80	75	71	79	74	71	78	74	70	76	73	70	69																												
7	86	77	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65																												
8	82	73	68	64	81	73	67	64	72	67	63	71	66	63	70	66	63	62																												
9	79	70	64	60	78	69	64	60	68	64	60	67	63	60	67	63	60	59																												
10	76	67	61	58	75	66	61	57	65	61	57	65	60	57	64	60	57	56																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	259574
5°	236809
10°	173160
15°	98514
20°	59972
25°	48589
30°	39873
35°	32210
40°	25455
45°	19343
50°	9808
55°	2198
60°	1360
65°	687
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19343 cd/sqm



TEST NUMBER: P642950

CATALOG NUMBER: ML5615LSNFL259FS1E - 693BB - 1500LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	371.8	21.1
10°-20°	498.8	28.2
20°-30°	370.0	21.0
30°-40°	301.9	17.1
40°-50°	184.5	10.4
50°-60°	33.3	1.9
60°-70°	5.4	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1240.5	70.3
0°-40°	1542.4	87.4
0°-60°	1760.3	99.7
0°-90°	1765.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1765.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4735	
5°	4303	372
15°	1736	499
25°	803	370
35°	481	302
45°	250	184
55°	23	33
65°	5	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P642950

CATALOG NUMBER: ML5615LSNFL259FS1E - 693BB - 1500LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	4735.0
2.5°	4639.5
5°	4303.3
7.5°	3760.1
10°	3110.7
12.5°	2387.0
15°	1735.8
17.5°	1281.1
20°	1028.0
22.5°	897.1
25°	803.3
27.5°	713.1
30°	629.9
32.5°	553.8
35°	481.3
37.5°	415.8
40°	355.7
42.5°	302.6
45°	249.5
47.5°	178.7
50°	115.0
52.5°	49.5
55°	23.0
57.5°	15.9
60°	12.4
62.5°	8.8
65°	5.3
67.5°	1.8
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)