

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642957

Luminaire Tested: ML5615LSNFL259FS1E - 693SNB - 1200LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642957
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-19)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSNFL259FS1E - 693SNB - 1200LM - 3000K
Description: ML56 RR, 25D TIR OPTIC, 6" SATIN NICKLE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1354.2 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642957

CATALOG NUMBER: ML5615LSNFL259FS1E - 693SNB - 1200LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P642957

CATALOG NUMBER: ML5615LSNFL259FS1E - 693SNB - 1200LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																			
3	103	97	92	88	101	96	91	88	93	89	86	90	87	85	88	86	84	82																			
4	98	91	86	82	96	90	85	81	88	83	80	86	82	79	84	81	78	77																			
5	94	86	80	76	92	85	79	75	83	78	75	81	77	74	80	76	73	72																			
6	89	81	75	71	88	80	75	71	78	74	70	77	73	70	76	72	69	68																			
7	85	76	71	67	84	76	70	66	74	70	66	73	69	66	72	68	65	64																			
8	82	73	67	63	80	72	67	63	71	66	63	70	66	62	69	65	62	61																			
9	78	69	63	60	77	69	63	60	68	63	59	67	62	59	66	62	59	58																			
10	75	66	60	57	74	65	60	57	65	60	57	64	59	56	63	59	56	55																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	193230
5°	176370
10°	129123
15°	74382
20°	45737
25°	37200
30°	30701
35°	25150
40°	20002
45°	15420
50°	8204
55°	2112
60°	1283
65°	675
70°	208
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15420 cd/sqm



TEST NUMBER: P642957

CATALOG NUMBER: ML5615LSNFL259FS1E - 693SNB - 1200LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	277.2	20.5
10°-20°	375.9	27.8
20°-30°	283.4	20.9
30°-40°	234.6	17.3
40°-50°	146.7	10.8
50°-60°	30.1	2.2
60°-70°	5.4	0.4
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	936.6	69.2
0°-40°	1171.1	86.5
0°-60°	1347.9	99.5
0°-90°	1354.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1354.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3525	
5°	3205	277
15°	1311	376
25°	615	283
35°	376	235
45°	199	147
55°	22	30
65°	5	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P642957

CATALOG NUMBER: ML5615LSNFL259FS1E - 693SNB - 1200LM - 3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	3524.8
2.5°	3454.6
5°	3205.0
7.5°	2808.4
10°	2319.6
12.5°	1789.1
15°	1310.6
17.5°	973.9
20°	784.0
22.5°	686.5
25°	615.0
27.5°	547.4
30°	485.0
32.5°	427.8
35°	375.8
37.5°	323.8
40°	279.5
42.5°	236.6
45°	198.9
47.5°	144.3
50°	96.2
52.5°	45.5
55°	22.1
57.5°	15.6
60°	11.7
62.5°	7.8
65°	5.2
67.5°	2.6
70°	1.3
72.5°	1.3
75°	0.0
77.5°	1.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)