

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643421

Luminaire Tested: ML5615LSVWFL9FS1E - 592SC - 1200LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643421
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-94)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL9FS1E - 592SC - 1200LM - 2700K
Description: ML56 RR, MILKY OPTIC, 5" SPECULAR CLEAR TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1278.7 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.95
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643421
CATALOG NUMBER: ML5615LSVWFL9FS1E - 592SC - 1200LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P643421

CATALOG NUMBER: ML5615LSVWFL9FS1E - 592SC - 1200LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93				93															
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85				85															
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	79	78				78															
4	95	87	81	76	93	86	80	76	83	79	75	81	77	74	79	76	73	71				71															
5	90	81	74	69	88	80	74	69	78	73	69	76	71	68	74	70	67	66				66															
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61				61															
7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	65	61	58	56				56															
8	76	65	59	54	74	65	59	54	64	58	54	63	57	54	62	57	54	52				52															
9	72	61	55	51	70	61	55	50	60	54	50	59	54	50	58	53	50	48				48															
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45				45															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	98234
5°	99013
10°	95293
15°	85060
20°	74363
25°	65544
30°	57864
35°	49110
40°	36232
45°	22451
50°	12109
55°	6097
60°	2795
65°	1177
70°	577
75°	397
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22451 cd/sqm



TEST NUMBER: P643421

CATALOG NUMBER: ML5615LSVWFL9FS1E - 592SC - 1200LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.4	9.2
10°-20°	290.4	22.7
20°-30°	345.9	27.1
30°-40°	312.3	24.4
40°-50°	160.6	12.6
50°-60°	43.6	3.4
60°-70°	7.1	0.6
70°-80°	1.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	753.7	58.9
0°-40°	1066.0	83.4
0°-60°	1270.2	99.3
0°-90°	1278.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1278.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1244	
5°	1250	117
15°	1041	290
25°	752	346
35°	510	312
45°	201	161
55°	44	44
65°	6	7
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P643421

CATALOG NUMBER: ML5615LSVWFL9FS1E - 592SC - 1200LM - 2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1244.4
2.5°	1246.9
5°	1249.5
7.5°	1233.0
10°	1188.8
12.5°	1121.7
15°	1040.8
17.5°	961.1
20°	885.2
22.5°	814.4
25°	752.5
27.5°	691.8
30°	634.8
32.5°	574.1
35°	509.6
37.5°	433.8
40°	351.6
42.5°	273.2
45°	201.1
47.5°	144.2
50°	98.6
52.5°	65.8
55°	44.3
57.5°	29.1
60°	17.7
62.5°	10.1
65°	6.3
67.5°	2.5
70°	2.5
72.5°	1.3
75°	1.3
77.5°	1.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)