

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643459

Luminaire Tested: ML5615LSVWFL9FS1E - 593BB - 1500LM - 4000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P643459  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-98)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSVWFL9FS1E - 593BB - 1500LM - 4000K  
Description: ML56 RR, MILKY OPTIC, 5" BLACK BAFFLE TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1231.2 lumens  
Efficiency: N/A  
Efficacy: 72.0 lumens/watt  
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.11  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 17.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P643459  
CATALOG NUMBER: ML5615LSVWFL9FS1E - 593BB - 1500LM - 4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P643459

CATALOG NUMBER: ML5615LSVWFL9FS1E - 593BB - 1500LM - 4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92																			
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84																			
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76																			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69																			
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63																			
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58																			
7	78	67	60	56	76	67	60	56	65	59	55	64	59	55	63	58	55	53																			
8	73	63	56	51	72	62	55	51	61	55	51	60	54	51	59	54	50	49																			
9	69	58	52	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45																			
10	65	54	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	48368
5°	48261
10°	47739
15°	46964
20°	45901
25°	44706
30°	42532
35°	37510
40°	27967
45°	17134
50°	9501
55°	4731
60°	2127
65°	687
70°	289
75°	381
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 17134 cd/sqm



TEST NUMBER: P643459

CATALOG NUMBER: ML5615LSVWFL9FS1E - 593BB - 1500LM - 4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	83.1	6.7
10°-20°	232.9	18.9
20°-30°	338.8	27.5
30°-40°	341.6	27.7
40°-50°	177.1	14.4
50°-60°	49.2	4.0
60°-70°	7.3	0.6
70°-80°	1.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	654.8	53.2
0°-40°	996.4	80.9
0°-60°	1222.6	99.3
0°-90°	1231.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1231.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	882	
5°	877	83
15°	828	233
25°	739	339
35°	560	342
45°	221	177
55°	50	49
65°	5	7
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P643459

CATALOG NUMBER: ML5615LSVWFL9FS1E - 593BB - 1500LM - 4000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	882.3
2.5°	880.5
5°	877.0
7.5°	868.2
10°	857.6
12.5°	843.4
15°	827.5
17.5°	808.0
20°	786.8
22.5°	763.8
25°	739.1
27.5°	709.0
30°	671.9
32.5°	624.2
35°	560.5
37.5°	480.9
40°	390.8
42.5°	298.8
45°	221.0
47.5°	159.1
50°	111.4
52.5°	76.0
55°	49.5
57.5°	31.8
60°	19.4
62.5°	10.6
65°	5.3
67.5°	3.5
70°	1.8
72.5°	1.8
75°	1.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)