

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643000

Luminaire Tested: ML5615LSNFL259FS1E - 693WB - 900LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643000
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSNFL259FS1E - 693WB - 900LM - 5000K
Description: ML56 RR, 25D TIR OPTIC, 6" WHITE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1213.4 lumens
Efficiency: N/A
Efficacy: 115.6 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643000
CATALOG NUMBER: ML5615LSNFL259FS1E - 693WB - 900LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P643000

CATALOG NUMBER: ML5615LSNFL259FS1E - 693WB - 900LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93																			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	90	84	80	95	88	83	79	86	82	78	84	81	77	82	79	77	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	71	68	66																			
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62																			
8	80	71	65	61	79	71	65	61	70	65	61	68	64	61	68	63	60	59																			
9	77	68	62	58	76	67	62	58	66	61	58	65	61	58	65	60	57	56																			
10	74	65	59	55	73	64	59	55	63	58	55	63	58	55	62	58	55	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	168161
5°	153466
10°	112824
15°	64291
20°	39612
25°	32337
30°	26637
35°	21844
40°	17497
45°	13753
50°	7855
55°	2829
60°	2368
65°	2062
70°	1827
75°	1927
80°	2147
85°	2139

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13753 cd/sqm



TEST NUMBER: P643000

CATALOG NUMBER: ML5615LSNFL259FS1E - 693WB - 900LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.4	19.9
10°-20°	326.7	26.9
20°-30°	246.1	20.3
30°-40°	204.2	16.8
40°-50°	131.6	10.8
50°-60°	34.9	2.9
60°-70°	15.6	1.3
70°-80°	9.6	0.8
80°-90°	3.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	814.1	67.1
0°-40°	1018.3	83.9
0°-60°	1184.8	97.6
0°-90°	1213.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1213.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3068	
5°	2789	241
15°	1133	327
25°	535	246
35°	326	204
45°	177	132
55°	30	35
65°	16	16
75°	9	10
85°	3	3
90°	0	



TEST NUMBER: P643000

CATALOG NUMBER: ML5615LSNFL259FS1E - 693WB - 900LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	3067.5
2.5°	3007.2
5°	2788.8
7.5°	2441.9
10°	2026.8
12.5°	1557.1
15°	1132.8
17.5°	847.3
20°	679.0
22.5°	596.0
25°	534.6
27.5°	475.4
30°	420.8
32.5°	371.9
35°	326.4
37.5°	283.2
40°	244.5
42.5°	210.4
45°	177.4
47.5°	131.9
50°	92.1
52.5°	47.8
55°	29.6
57.5°	23.9
60°	21.6
62.5°	18.2
65°	15.9
67.5°	12.5
70°	11.4
72.5°	10.2
75°	9.1
77.5°	8.0
80°	6.8
82.5°	4.5
85°	3.4
87.5°	1.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)