

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643037

Luminaire Tested: ML5615LSNFL259FS1E - 696WB - 1500LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643037
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-23)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSNFL259FS1E - 696WB - 1500LM - 3000K
Description: ML56 RR, 25D TIR OPTIC, 6" SHALLOW WHITE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1738.5 lumens
Efficiency: N/A
Efficacy: 101.7 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643037
CATALOG NUMBER: ML5615LSNFL259FS1E - 696WB - 1500LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P643037

CATALOG NUMBER: ML5615LSNFL259FS1E - 696WB - 1500LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	87	84	81	80																			
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	78	76	74																			
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69																			
6	87	78	72	68	86	78	72	68	76	71	67	75	70	67	73	70	67	65																			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61																			
8	80	70	64	60	78	70	64	60	69	63	60	68	63	60	67	62	59	58																			
9	76	67	61	57	75	66	61	57	65	60	57	64	60	57	64	59	56	55																			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	236209
5°	216965
10°	159043
15°	91374
20°	55124
25°	44488
30°	36436
35°	29533
40°	23687
45°	18839
50°	14865
55°	10389
60°	4561
65°	2698
70°	2052
75°	1694
80°	1515
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18839 cd/sqm



TEST NUMBER: P643037

CATALOG NUMBER: ML5615LSNFL259FS1E - 696WB - 1500LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	340.9	19.6
10°-20°	460.7	26.5
20°-30°	339.2	19.5
30°-40°	277.1	15.9
40°-50°	189.3	10.9
50°-60°	96.5	5.6
60°-70°	22.9	1.3
70°-80°	8.6	0.5
80°-90°	3.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1140.8	65.6
0°-40°	1417.9	81.6
0°-60°	1703.7	98.0
0°-90°	1738.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1738.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4309	
5°	3943	341
15°	1610	461
25°	736	339
35°	441	277
45°	243	189
55°	109	97
65°	21	23
75°	8	9
85°	3	3
90°	0	



TEST NUMBER: P643037

CATALOG NUMBER: ML5615LSNFL259FS1E - 696WB - 1500LM - 3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	4308.8
2.5°	4227.3
5°	3942.7
7.5°	3459.8
10°	2857.1
12.5°	2204.8
15°	1610.0
17.5°	1184.7
20°	944.9
22.5°	825.0
25°	735.5
27.5°	652.3
30°	575.6
32.5°	505.2
35°	441.3
37.5°	383.7
40°	331.0
42.5°	284.6
45°	243.0
47.5°	206.2
50°	174.3
52.5°	145.5
55°	108.7
57.5°	73.5
60°	41.6
62.5°	27.2
65°	20.8
67.5°	17.6
70°	12.8
72.5°	9.6
75°	8.0
77.5°	6.4
80°	4.8
82.5°	4.8
85°	3.2
87.5°	1.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)