

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643500

Luminaire Tested: ML5615LSVWFL9FS1E - 593WB - 1200LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643500
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-97)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL9FS1E - 593WB - 1200LM - 5000K
Description: ML56 RR, MILKY OPTIC, 5" WHITE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1393.5 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.14
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643500
CATALOG NUMBER: ML5615LSVWFL9FS1E - 593WB - 1200LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P643500

CATALOG NUMBER: ML5615LSVWFL9FS1E - 593WB - 1200LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89																			
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	86	83	80	78																			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	71	69																			
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62																			
5	84	73	65	60	82	72	65	59	70	63	59	68	62	58	66	61	58	56																			
6	78	67	59	54	76	66	59	53	64	58	53	63	57	53	61	56	52	50																			
7	73	61	54	49	72	61	54	48	59	53	48	58	52	48	57	51	48	46																			
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42																			
9	65	53	45	41	63	52	45	41	51	45	40	50	44	40	49	44	40	38																			
10	61	49	42	37	60	49	42	37	48	41	37	47	41	37	46	41	37	35																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	64937
5°	64725
10°	63983
15°	62994
20°	61854
25°	60501
30°	58201
35°	52666
40°	41787
45°	29707
50°	21197
55°	16433
60°	14083
65°	13169
70°	12602
75°	12292
80°	11774
85°	10416

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 29707 cd/sqm



TEST NUMBER: P643500

CATALOG NUMBER: ML5615LSVWFL9FS1E - 593WB - 1200LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.4	5.6
10°-20°	217.1	15.6
20°-30°	319.1	22.9
30°-40°	334.3	24.0
40°-50°	210.3	15.1
50°-60°	110.6	7.9
60°-70°	70.1	5.0
70°-80°	42.1	3.0
80°-90°	12.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	613.6	44.0
0°-40°	947.9	68.0
0°-60°	1268.8	91.1
0°-90°	1393.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1393.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	823	
5°	817	77
15°	771	217
25°	695	319
35°	546	334
45°	266	210
55°	119	111
65°	70	70
75°	40	42
85°	12	13
90°	0	



TEST NUMBER: P643500

CATALOG NUMBER: ML5615LSVWFL9FS1E - 593WB - 1200LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	822.6
2.5°	821.2
5°	816.8
7.5°	809.7
10°	798.2
12.5°	785.2
15°	770.8
17.5°	753.6
20°	736.3
22.5°	716.2
25°	694.6
27.5°	670.2
30°	638.5
32.5°	598.3
35°	546.5
37.5°	480.3
40°	405.5
42.5°	330.8
45°	266.1
47.5°	212.8
50°	172.6
52.5°	142.4
55°	119.4
57.5°	103.5
60°	89.2
62.5°	79.1
65°	70.5
67.5°	61.8
70°	54.6
72.5°	47.5
75°	40.3
77.5°	31.6
80°	25.9
82.5°	17.3
85°	11.5
87.5°	4.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)