

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643502

Luminaire Tested: ML5615LSVWFL9FS1E - 593WB - 1500LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643502
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-97)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL9FS1E - 593WB - 1500LM - 3000K
Description: ML56 RR, MILKY OPTIC, 5" WHITE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1549.5 lumens
Efficiency: N/A
Efficacy: 90.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.14
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643502
CATALOG NUMBER: ML5615LSVWFL9FS1E - 593WB - 1500LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P643502

CATALOG NUMBER: ML5615LSVWFL9FS1E - 593WB - 1500LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89																			
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	86	83	80	78																			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	71	69																			
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62																			
5	84	73	65	60	82	72	65	59	70	63	59	68	62	58	66	61	58	56																			
6	78	67	59	54	76	66	59	53	64	58	53	63	57	53	61	56	52	50																			
7	73	61	54	49	72	61	54	48	59	53	48	58	52	48	57	51	48	46																			
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42																			
9	65	53	45	41	63	52	45	41	51	45	40	50	44	40	49	44	40	38																			
10	61	49	42	37	60	49	42	37	48	41	37	47	41	37	46	41	37	35																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	72207
5°	71976
10°	71141
15°	70047
20°	68777
25°	67277
30°	64719
35°	58563
40°	46465
45°	33023
50°	23567
55°	18263
60°	15646
65°	14644
70°	14033
75°	13664
80°	13093
85°	11594

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 33023 cd/sqm



TEST NUMBER: P643502

CATALOG NUMBER: ML5615LSVWFL9FS1E - 593WB - 1500LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.1	5.6
10°-20°	241.4	15.6
20°-30°	354.8	22.9
30°-40°	371.8	24.0
40°-50°	233.8	15.1
50°-60°	122.9	7.9
60°-70°	77.9	5.0
70°-80°	46.8	3.0
80°-90°	13.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	682.3	44.0
0°-40°	1054.0	68.0
0°-60°	1410.8	91.0
0°-90°	1549.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1549.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	915	
5°	908	86
15°	857	241
25°	772	355
35°	608	372
45°	296	234
55°	133	123
65°	78	78
75°	45	47
85°	13	14
90°	0	



TEST NUMBER: P643502

CATALOG NUMBER: ML5615LSVWFL9FS1E - 593WB - 1500LM - 3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	914.7
2.5°	913.1
5°	908.3
7.5°	900.3
10°	887.5
12.5°	873.1
15°	857.1
17.5°	837.9
20°	818.7
22.5°	796.3
25°	772.4
27.5°	745.2
30°	710.0
32.5°	665.2
35°	607.7
37.5°	534.1
40°	450.9
42.5°	367.8
45°	295.8
47.5°	236.7
50°	191.9
52.5°	158.3
55°	132.7
57.5°	115.1
60°	99.1
62.5°	87.9
65°	78.4
67.5°	68.8
70°	60.8
72.5°	52.8
75°	44.8
77.5°	35.2
80°	28.8
82.5°	19.2
85°	12.8
87.5°	4.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)