

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643528

Luminaire Tested: ML5615LSVWFL9FS1E - 594TBZB - 1200LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643528
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-103)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL9FS1E - 594TBZB - 1200LM - 3500K
Description: ML56 RR, MILKY OPTIC, 5" TUSCON BRONZE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1424.5 lumens
Efficiency: N/A
Efficacy: 106.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.27
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643528

CATALOG NUMBER: ML5615LSVWFL9FS1E - 594TBZB - 1200LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P643528

CATALOG NUMBER: ML5615LSVWFL9FS1E - 594TBZB - 1200LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	110	106	102	99	107	104	100	97	100	97	94	96	93	91	92	90	89	87			87
2	101	94	88	83	99	92	87	82	89	84	80	85	82	78	82	79	76	74			74
3	93	84	76	70	91	82	75	70	79	73	69	77	72	67	74	70	66	64			64
4	86	75	67	61	84	74	66	60	71	65	60	69	63	59	67	62	58	56			56
5	79	68	59	53	77	67	59	53	64	58	52	63	57	52	61	55	51	49			49
6	74	61	53	47	72	60	52	47	59	52	46	57	51	46	55	50	46	44			44
7	69	56	48	42	67	55	47	42	54	47	41	52	46	41	51	45	41	39			39
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35			35
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	43	38	34	32			32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29			29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	50222
5°	50097
10°	49923
15°	49591
20°	48959
25°	48080
30°	46661
35°	44821
40°	42014
45°	38795
50°	34804
55°	30347
60°	25751
65°	21462
70°	17888
75°	15494
80°	13365
85°	13314

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 38795 cd/sqm



TEST NUMBER: P643528

CATALOG NUMBER: ML5615LSVWFL9FS1E - 594TBZB - 1200LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.1	4.2
10°-20°	170.9	12.0
20°-30°	253.7	17.8
30°-40°	289.5	20.3
40°-50°	267.2	18.8
50°-60°	197.4	13.9
60°-70°	115.2	8.1
70°-80°	54.3	3.8
80°-90°	16.4	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	484.6	34.0
0°-40°	774.1	54.3
0°-60°	1238.7	87.0
0°-90°	1424.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1424.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	636	
5°	632	60
15°	607	171
25°	552	254
35°	465	289
45°	348	267
55°	220	197
65°	115	115
75°	51	54
85°	15	16
90°	0	



TEST NUMBER: P643528

CATALOG NUMBER: ML5615LSVWFL9FS1E - 594TBZB - 1200LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	636.2
2.5°	634.9
5°	632.2
7.5°	628.2
10°	622.8
12.5°	614.8
15°	606.8
17.5°	594.8
20°	582.8
22.5°	568.0
25°	552.0
27.5°	533.3
30°	511.9
32.5°	489.2
35°	465.1
37.5°	437.1
40°	407.7
42.5°	378.3
45°	347.5
47.5°	315.4
50°	283.4
52.5°	251.3
55°	220.5
57.5°	189.8
60°	163.1
62.5°	136.3
65°	114.9
67.5°	94.9
70°	77.5
72.5°	62.8
75°	50.8
77.5°	38.8
80°	29.4
82.5°	21.4
85°	14.7
87.5°	9.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)