

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643072

Luminaire Tested: ML5615LSVWFL759FS1E - 592H - 900LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643072
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-72)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL759FS1E - 592H - 900LM - 3000K
Description: ML56 RR, 75D TIR OPTIC, 5" HAZE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1110.9 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.07
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643072

CATALOG NUMBER: ML5615LSVWFL759FS1E - 592H - 900LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P643072

CATALOG NUMBER: ML5615LSVWFL759FS1E - 592H - 900LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	101	97	93	105	100	96	92	96	93	90	93	91	88	91	88	87	85			85																
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78			78																
4	95	87	81	76	93	85	80	75	83	78	75	81	77	74	79	76	73	71			71																
5	89	80	74	69	88	79	73	69	77	72	68	76	71	68	74	70	67	65			65																
6	84	74	68	63	83	74	67	63	72	67	63	71	66	62	69	65	62	60			60																
7	79	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55			55																
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51																
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48																
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44			44																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	65276
5°	65763
10°	66692
15°	68331
20°	68600
25°	65126
30°	58311
35°	46874
40°	31049
45°	15272
50°	8965
55°	5244
60°	1784
65°	392
70°	231
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15272 cd/sqm



TEST NUMBER: P643072

CATALOG NUMBER: ML5615LSVWFL759FS1E - 592H - 900LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.3	7.1
10°-20°	235.6	21.2
20°-30°	340.3	30.6
30°-40°	297.1	26.7
40°-50°	119.4	10.7
50°-60°	35.0	3.2
60°-70°	3.8	0.3
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	655.2	59.0
0°-40°	952.3	85.7
0°-60°	1106.7	99.6
0°-90°	1110.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1110.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	827	
5°	830	79
15°	836	236
25°	748	340
35°	486	297
45°	137	119
55°	38	35
65°	2	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P643072

CATALOG NUMBER: ML5615LSVWFL759FS1E - 592H - 900LM - 3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	826.9
2.5°	827.9
5°	829.9
7.5°	831.0
10°	832.0
12.5°	834.1
15°	836.1
17.5°	832.0
20°	816.6
22.5°	787.8
25°	747.7
27.5°	698.3
30°	639.7
32.5°	568.7
35°	486.4
37.5°	392.9
40°	301.3
42.5°	211.9
45°	136.8
47.5°	93.6
50°	73.0
52.5°	53.5
55°	38.1
57.5°	24.7
60°	11.3
62.5°	6.2
65°	2.1
67.5°	1.0
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)