

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643556

Luminaire Tested: ML5615LSVWFL9FS1E - 596WB - 1200LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643556
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-104)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL9FS1E - 596WB - 1200LM - 2700K
Description: ML56 RR, MILKY OPTIC, 5" SHALLOW WHITE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1287.5 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.24
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643556
CATALOG NUMBER: ML5615LSVWFL9FS1E - 596WB - 1200LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P643556

CATALOG NUMBER: ML5615LSVWFL9FS1E - 596WB - 1200LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	98	96	97	95	93	94	92	91	89																			
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78																			
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69																			
4	89	79	71	66	87	77	71	65	75	69	64	73	68	64	71	66	63	61																			
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54																			
6	77	65	58	52	75	64	57	52	63	56	51	61	55	51	60	55	51	49																			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44																			
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40																			
9	63	51	44	39	62	50	43	39	49	43	38	48	42	38	47	42	38	36																			
10	59	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53285
5°	53291
10°	52993
15°	52484
20°	51824
25°	50867
30°	49660
35°	47510
40°	43116
45°	35144
50°	25766
55°	18442
60°	13767
65°	11095
70°	9625
75°	9242
80°	9183
85°	7971

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 35144 cd/sqm



TEST NUMBER: P643556

CATALOG NUMBER: ML5615LSVWFL9FS1E - 596WB - 1200LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.8	5.0
10°-20°	181.1	14.1
20°-30°	269.0	20.9
30°-40°	305.6	23.7
40°-50°	241.1	18.7
50°-60°	124.1	9.6
60°-70°	60.3	4.7
70°-80°	32.2	2.5
80°-90°	10.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	513.9	39.9
0°-40°	819.5	63.7
0°-60°	1184.7	92.0
0°-90°	1287.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1287.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	675	
5°	672	64
15°	642	181
25°	584	269
35°	493	306
45°	315	241
55°	134	124
65°	59	60
75°	30	32
85°	9	10
90°	0	



TEST NUMBER: P643556

CATALOG NUMBER: ML5615LSVWFL9FS1E - 596WB - 1200LM - 2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	675.0
2.5°	675.0
5°	672.5
7.5°	667.4
10°	661.1
12.5°	652.3
15°	642.2
17.5°	630.8
20°	616.9
22.5°	601.7
25°	584.0
27.5°	566.3
30°	544.8
32.5°	520.8
35°	493.0
37.5°	460.1
40°	418.4
42.5°	369.1
45°	314.8
47.5°	259.1
50°	209.8
52.5°	168.1
55°	134.0
57.5°	107.4
60°	87.2
62.5°	70.8
65°	59.4
67.5°	49.3
70°	41.7
72.5°	35.4
75°	30.3
77.5°	25.3
80°	20.2
82.5°	15.2
85°	8.8
87.5°	3.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)