

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643111

Luminaire Tested: ML5615LSVWFL759FS1E - 593BB - 1500LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P643111  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-75)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSVWFL759FS1E - 593BB - 1500LM - 2700K  
Description: ML56 RR, 75D TIR OPTIC, 5" BLACK BAFFLE TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1596.9 lumens  
Efficiency: N/A  
Efficacy: 93.4 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.09  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct

Input Watts (W): 17.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P643111  
CATALOG NUMBER: ML5615LSVWFL759FS1E - 593BB - 1500LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P643111

CATALOG NUMBER: ML5615LSVWFL759FS1E - 593BB - 1500LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92	92	92	92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85	85	85	85
3	101	94	88	84	99	92	87	83	90	85	82	87	83	81	85	82	79	78	78	78	78
4	95	87	80	76	93	85	80	75	83	78	74	81	77	74	79	76	73	71	71	71	71
5	89	80	74	69	88	79	73	69	77	72	68	76	71	67	74	70	67	65	65	65	65
6	84	74	68	63	83	74	67	63	72	66	62	71	66	62	69	65	61	60	60	60	60
7	79	69	63	58	78	68	62	58	67	62	57	66	61	57	65	60	57	55	55	55	55
8	75	64	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51	51	51	51
9	71	60	54	49	70	60	54	49	59	53	49	58	53	49	57	52	49	47	47	47	47
10	67	56	50	46	66	56	50	46	55	50	46	54	49	46	54	49	45	44	44	44	44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	89535
5°	90859
10°	93657
15°	97401
20°	98675
25°	93913
30°	84244
35°	67921
40°	45538
45°	22752
50°	12797
55°	7707
60°	2700
65°	299
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 22752 cd/sqm



TEST NUMBER: P643111

CATALOG NUMBER: ML5615LSVWFL759FS1E - 593BB - 1500LM - 2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	110.1	6.9
10°-20°	335.8	21.0
20°-30°	490.9	30.7
30°-40°	429.9	26.9
40°-50°	174.6	10.9
50°-60°	50.9	3.2
60°-70°	4.7	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	936.8	58.7
0°-40°	1366.7	85.6
0°-60°	1592.2	99.7
0°-90°	1596.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1596.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1134	
5°	1147	110
15°	1192	336
25°	1078	491
35°	705	430
45°	204	175
55°	56	51
65°	2	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P643111

CATALOG NUMBER: ML5615LSVWFL759FS1E - 593BB - 1500LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1134.2
2.5°	1137.3
5°	1146.6
7.5°	1157.5
10°	1168.4
12.5°	1180.9
15°	1191.8
17.5°	1191.8
20°	1174.6
22.5°	1135.8
25°	1078.2
27.5°	1008.2
30°	924.2
32.5°	819.9
35°	704.8
37.5°	567.9
40°	441.9
42.5°	308.1
45°	203.8
47.5°	135.4
50°	104.2
52.5°	77.8
55°	56.0
57.5°	35.8
60°	17.1
62.5°	9.3
65°	1.6
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)