

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643562

Luminaire Tested: ML5615LSVWFL9FS1E - 596WB - 1500LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643562
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-104)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL9FS1E - 596WB - 1500LM - 3000K
Description: ML56 RR, MILKY OPTIC, 5" SHALLOW WHITE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1628.2 lumens
Efficiency: N/A
Efficacy: 95.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.24
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643562

CATALOG NUMBER: ML5615LSVWFL9FS1E - 596WB - 1500LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P643562

CATALOG NUMBER: ML5615LSVWFL9FS1E - 596WB - 1500LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	98	96	97	95	93	94	92	91	89																			
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78																			
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69																			
4	89	79	71	66	87	77	71	65	75	69	64	73	68	64	71	66	63	61																			
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54																			
6	77	65	58	52	75	64	57	52	63	56	51	61	55	51	60	55	51	49																			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44																			
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40																			
9	63	51	44	39	62	50	43	39	49	43	38	48	42	38	47	42	38	36																			
10	59	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	67384
5°	67388
10°	67013
15°	66361
20°	65534
25°	64325
30°	62804
35°	60076
40°	54524
45°	44432
50°	32594
55°	23314
60°	17414
65°	14028
70°	12187
75°	11712
80°	11638
85°	10144

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 44432 cd/sqm



TEST NUMBER: P643562

CATALOG NUMBER: ML5615LSVWFL9FS1E - 596WB - 1500LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.7	5.0
10°-20°	229.0	14.1
20°-30°	340.1	20.9
30°-40°	386.5	23.7
40°-50°	304.9	18.7
50°-60°	157.0	9.6
60°-70°	76.2	4.7
70°-80°	40.7	2.5
80°-90°	13.1	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	649.8	39.9
0°-40°	1036.3	63.6
0°-60°	1498.2	92.0
0°-90°	1628.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1628.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	854	
5°	850	81
15°	812	229
25°	738	340
35°	623	386
45°	398	305
55°	169	157
65°	75	76
75°	38	41
85°	11	13
90°	0	



TEST NUMBER: P643562

CATALOG NUMBER: ML5615LSVWFL9FS1E - 596WB - 1500LM - 3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	853.6
2.5°	853.6
5°	850.4
7.5°	844.0
10°	836.0
12.5°	824.8
15°	812.0
17.5°	797.7
20°	780.1
22.5°	760.9
25°	738.5
27.5°	716.1
30°	689.0
32.5°	658.6
35°	623.4
37.5°	581.9
40°	529.1
42.5°	466.8
45°	398.0
47.5°	327.7
50°	265.4
52.5°	212.6
55°	169.4
57.5°	135.9
60°	110.3
62.5°	89.5
65°	75.1
67.5°	62.3
70°	52.8
72.5°	44.8
75°	38.4
77.5°	32.0
80°	25.6
82.5°	19.2
85°	11.2
87.5°	4.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)