

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643122

Luminaire Tested: ML5615LSVWFL759FS1E - 593SNB - 1200LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643122
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL759FS1E - 593SNB - 1200LM - 3000K
Description: ML56 RR, 75D TIR OPTIC, 5" SATIN NICKLE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1372.4 lumens
Efficiency: N/A
Efficacy: 102.4 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.09
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643122
CATALOG NUMBER: ML5615LSVWFL759FS1E - 593SNB - 1200LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P643122

CATALOG NUMBER: ML5615LSVWFL759FS1E - 593SNB - 1200LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92					92			
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84					84			
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77					77			
4	95	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	71					71			
5	89	80	73	68	87	79	73	68	77	72	67	75	70	67	74	69	66	65					65			
6	84	74	67	63	82	73	67	62	72	66	62	70	65	61	69	64	61	59					59			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55					55			
8	75	64	57	53	73	63	57	53	62	57	52	61	56	52	60	55	52	50					50			
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47					47			
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	43					43			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	75704
5°	76818
10°	79165
15°	82200
20°	83512
25°	79567
30°	71400
35°	57812
40°	39025
45°	20486
50°	11827
55°	7336
60°	3284
65°	971
70°	600
75°	397
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20486 cd/sqm



TEST NUMBER: P643122

CATALOG NUMBER: ML5615LSVWFL759FS1E - 593SNB - 1200LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.1	6.8
10°-20°	283.7	20.7
20°-30°	415.7	30.3
30°-40°	367.2	26.8
40°-50°	155.0	11.3
50°-60°	49.0	3.6
60°-70°	7.3	0.5
70°-80°	1.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	792.5	57.7
0°-40°	1159.8	84.5
0°-60°	1363.8	99.4
0°-90°	1372.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1372.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	959	
5°	969	93
15°	1006	284
25°	914	416
35°	600	367
45°	184	155
55°	53	49
65°	5	7
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P643122

CATALOG NUMBER: ML5615LSVWFL759FS1E - 593SNB - 1200LM - 3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	959.0
2.5°	961.6
5°	969.4
7.5°	978.5
10°	987.6
12.5°	996.7
15°	1005.8
17.5°	1007.1
20°	994.1
22.5°	960.3
25°	913.5
27.5°	854.9
30°	783.3
32.5°	700.1
35°	599.9
37.5°	489.3
40°	378.7
42.5°	272.0
45°	183.5
47.5°	123.6
50°	96.3
52.5°	72.9
55°	53.3
57.5°	36.4
60°	20.8
62.5°	10.4
65°	5.2
67.5°	2.6
70°	2.6
72.5°	1.3
75°	1.3
77.5°	1.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)