

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643125

Luminaire Tested: ML5615LSVWFL759FS1E - 593SNB - 1200LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643125
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL759FS1E - 593SNB - 1200LM - 5000K
Description: ML56 RR, 75D TIR OPTIC, 5" SATIN NICKLE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1517.5 lumens
Efficiency: N/A
Efficacy: 113.2 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.09
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643125
CATALOG NUMBER: ML5615LSVWFL759FS1E - 593SNB - 1200LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P643125

CATALOG NUMBER: ML5615LSVWFL759FS1E - 593SNB - 1200LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92																			
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84																			
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77																			
4	95	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	71																			
5	89	80	73	68	87	79	73	68	77	72	67	75	70	67	74	69	66	65																			
6	84	74	67	63	82	73	67	62	72	66	62	70	65	61	69	64	61	59																			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55																			
8	75	64	57	53	73	63	57	53	62	57	52	61	56	52	60	55	52	50																			
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47																			
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	43																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	83701
5°	84932
10°	87533
15°	90887
20°	92341
25°	87973
30°	78948
35°	63912
40°	43147
45°	22652
50°	13079
55°	8120
60°	3631
65°	1083
70°	669
75°	427
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22652 cd/sqm



TEST NUMBER: P643125

CATALOG NUMBER: ML5615LSVWFL759FS1E - 593SNB - 1200LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.0	6.8
10°-20°	313.7	20.7
20°-30°	459.7	30.3
30°-40°	406.0	26.8
40°-50°	171.4	11.3
50°-60°	54.2	3.6
60°-70°	8.1	0.5
70°-80°	1.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	876.3	57.7
0°-40°	1282.3	84.5
0°-60°	1507.9	99.4
0°-90°	1517.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1517.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1060	
5°	1072	103
15°	1112	314
25°	1010	460
35°	663	406
45°	203	171
55°	59	54
65°	6	8
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P643125

CATALOG NUMBER: ML5615LSVWFL759FS1E - 593SNB - 1200LM - 5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1060.3
2.5°	1063.2
5°	1071.8
7.5°	1081.9
10°	1092.0
12.5°	1102.1
15°	1112.1
17.5°	1113.6
20°	1099.2
22.5°	1061.8
25°	1010.0
27.5°	945.2
30°	866.1
32.5°	774.0
35°	663.2
37.5°	541.0
40°	418.7
42.5°	300.7
45°	202.9
47.5°	136.7
50°	106.5
52.5°	80.6
55°	59.0
57.5°	40.3
60°	23.0
62.5°	11.5
65°	5.8
67.5°	2.9
70°	2.9
72.5°	1.4
75°	1.4
77.5°	1.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)