

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643590

Luminaire Tested: ML5615LSVWFL9FS1E - 692H - 1200LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643590
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-107)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL9FS1E - 692H - 1200LM - 5000K
Description: ML56 RR, MILKY OPTIC, 6" HAZE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1402.4 lumens
Efficiency: N/A
Efficacy: 104.7 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.1
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643590
CATALOG NUMBER: ML5615LSVWFL9FS1E - 692H - 1200LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P643590

CATALOG NUMBER: ML5615LSVWFL9FS1E - 692H - 1200LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83																			
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75																			
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	72	69	67																			
5	87	77	70	65	85	76	70	65	74	68	64	72	67	64	71	66	63	61																			
6	81	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	57	56																			
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51																			
8	72	61	54	49	71	60	54	49	59	53	49	58	53	49	57	52	48	47																			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43																			
10	64	53	46	42	63	52	46	42	52	46	42	51	45	41	50	45	41	40																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	56289
5°	55712
10°	54118
15°	51504
20°	48491
25°	45408
30°	42329
35°	39076
40°	33549
45°	24080
50°	14592
55°	8248
60°	4419
65°	2050
70°	1154
75°	911
80°	442
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24080 cd/sqm



TEST NUMBER: P643590

CATALOG NUMBER: ML5615LSVWFL9FS1E - 692H - 1200LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.4	6.8
10°-20°	254.6	18.2
20°-30°	345.2	24.6
30°-40°	361.1	25.8
40°-50°	240.2	17.1
50°-60°	82.6	5.9
60°-70°	18.5	1.3
70°-80°	4.2	0.3
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	695.1	49.6
0°-40°	1056.3	75.3
0°-60°	1379.1	98.3
0°-90°	1402.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1402.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1027	
5°	1012	95
15°	908	255
25°	751	345
35°	584	361
45°	311	240
55°	86	83
65°	16	19
75°	4	4
85°	0	1
90°	0	



TEST NUMBER: P643590

CATALOG NUMBER: ML5615LSVWFL9FS1E - 692H - 1200LM - 5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1026.8
2.5°	1023.9
5°	1012.4
7.5°	995.2
10°	972.2
12.5°	942.0
15°	907.5
17.5°	870.1
20°	831.2
22.5°	791.0
25°	750.7
27.5°	710.4
30°	668.7
32.5°	628.5
35°	583.9
37.5°	533.5
40°	468.8
42.5°	392.6
45°	310.6
47.5°	234.4
50°	171.1
52.5°	122.2
55°	86.3
57.5°	59.0
60°	40.3
62.5°	25.9
65°	15.8
67.5°	10.1
70°	7.2
72.5°	4.3
75°	4.3
77.5°	2.9
80°	1.4
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)