

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643138

Luminaire Tested: ML5615LSVWFL759FS1E - 593TBZB - 1200LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643138
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-77)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL759FS1E - 593TBZB - 1200LM - 3500K
Description: ML56 RR, 75D TIR OPTIC, 5" TUSCON BRONZE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1379.1 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.09
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643138
CATALOG NUMBER: ML5615LSVWFL759FS1E - 593TBZB - 1200LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P643138

CATALOG NUMBER: ML5615LSVWFL759FS1E - 593TBZB - 1200LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			92																
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85			85																
3	101	94	88	84	99	92	87	83	89	85	82	87	83	80	85	82	79	78			78																
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71			71																
5	89	80	74	69	88	79	73	69	77	72	68	76	71	67	74	70	67	65			65																
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60			60																
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55																
8	75	64	58	53	74	64	58	53	63	57	53	62	56	53	61	56	52	51			51																
9	71	60	54	49	70	60	53	49	59	53	49	58	53	49	57	52	49	47			47																
10	67	56	50	46	66	56	50	46	55	49	46	54	49	45	53	49	45	44			44																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	77220
5°	78363
10°	80768
15°	83875
20°	85099
25°	81013
30°	72722
35°	58342
40°	39252
45°	19392
50°	11323
55°	6799
60°	2321
65°	504
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19392 cd/sqm



TEST NUMBER: P643138

CATALOG NUMBER: ML5615LSVWFL759FS1E - 593TBZB - 1200LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.0	6.9
10°-20°	289.4	21.0
20°-30°	423.3	30.7
30°-40°	371.1	26.9
40°-50°	150.6	10.9
50°-60°	44.9	3.3
60°-70°	4.7	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	807.7	58.6
0°-40°	1178.9	85.5
0°-60°	1374.4	99.7
0°-90°	1379.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1379.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	978	
5°	989	95
15°	1026	289
25°	930	423
35°	605	371
45°	174	151
55°	49	45
65°	3	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P643138

CATALOG NUMBER: ML5615LSVWFL759FS1E - 593TBZB - 1200LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	978.2
2.5°	980.9
5°	988.9
7.5°	998.3
10°	1007.6
12.5°	1017.0
15°	1026.3
17.5°	1027.7
20°	1013.0
22.5°	978.2
25°	930.1
27.5°	870.0
30°	797.8
32.5°	709.6
35°	605.4
37.5°	491.8
40°	380.9
42.5°	265.9
45°	173.7
47.5°	117.6
50°	92.2
52.5°	68.2
55°	49.4
57.5°	32.1
60°	14.7
62.5°	8.0
65°	2.7
67.5°	1.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)