

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643594

Luminaire Tested: ML5615LSVWFL9FS1E - 692H - 1500LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643594
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-107)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL9FS1E - 692H - 1500LM - 4000K
Description: ML56 RR, MILKY OPTIC, 6" HAZE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1723.5 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.1
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643594
CATALOG NUMBER: ML5615LSVWFL9FS1E - 692H - 1500LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P643594

CATALOG NUMBER: ML5615LSVWFL9FS1E - 692H - 1500LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			91																
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83			83																
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75			75																
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	72	69	67			67																
5	87	77	70	65	85	76	70	65	74	68	64	72	67	64	71	66	63	61			61																
6	81	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	57	56			56																
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51			51																
8	72	61	54	49	71	60	54	49	59	53	49	58	53	49	57	52	48	47			47																
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			43																
10	64	53	46	42	63	52	46	42	52	46	42	51	45	41	50	45	41	40			40																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	69178
5°	68468
10°	66510
15°	63292
20°	59593
25°	55806
30°	52021
35°	48024
40°	41234
45°	29600
50°	17935
55°	10131
60°	5427
65°	2516
70°	1410
75°	1123
80°	568
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 29600 cd/sqm



TEST NUMBER: P643594

CATALOG NUMBER: ML5615LSVWFL9FS1E - 692H - 1500LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.2	6.8
10°-20°	312.9	18.2
20°-30°	424.2	24.6
30°-40°	443.8	25.8
40°-50°	295.3	17.1
50°-60°	101.5	5.9
60°-70°	22.8	1.3
70°-80°	5.1	0.3
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	854.3	49.6
0°-40°	1298.1	75.3
0°-60°	1694.9	98.3
0°-90°	1723.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1723.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1262	
5°	1244	117
15°	1115	313
25°	923	424
35°	718	444
45°	382	295
55°	106	101
65°	19	23
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P643594

CATALOG NUMBER: ML5615LSVWFL9FS1E - 692H - 1500LM - 4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1261.9
2.5°	1258.4
5°	1244.2
7.5°	1223.0
10°	1194.8
12.5°	1157.6
15°	1115.2
17.5°	1069.3
20°	1021.5
22.5°	972.1
25°	922.6
27.5°	873.1
30°	821.8
32.5°	772.3
35°	717.6
37.5°	655.7
40°	576.2
42.5°	482.5
45°	381.8
47.5°	288.1
50°	210.3
52.5°	150.2
55°	106.0
57.5°	72.5
60°	49.5
62.5°	31.8
65°	19.4
67.5°	12.4
70°	8.8
72.5°	5.3
75°	5.3
77.5°	3.5
80°	1.8
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)