

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643609

Luminaire Tested: ML5615LSVWFL9FS1E - 692SC - 1500LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643609
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-106)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL9FS1E - 692SC - 1500LM - 4000K
Description: ML56 RR, MILKY OPTIC, 6" SPECULAR CLEAR TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1831.3 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.69
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643609

CATALOG NUMBER: ML5615LSVWFL9FS1E - 692SC - 1500LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P643609

CATALOG NUMBER: ML5615LSVWFL9FS1E - 692SC - 1500LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93			93																
2	107	102	97	93	105	100	96	92	97	93	90	93	91	88	91	89	87	85			85																
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78			78																
4	95	87	81	76	93	86	80	76	83	79	75	81	77	74	79	76	73	71			71																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66			66																
6	85	75	69	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			61																
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56																
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52																
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49			49																
10	68	58	52	48	67	58	52	48	57	51	48	56	51	47	55	51	47	46			46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	142450
5°	133166
10°	108905
15°	82821
20°	66150
25°	56386
30°	49603
35°	44276
40°	37721
45°	26607
50°	15539
55°	8114
60°	3684
65°	1141
70°	289
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 26607 cd/sqm



TEST NUMBER: P643609

CATALOG NUMBER: ML5615LSVWFL9FS1E - 692SC - 1500LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.9	11.8
10°-20°	411.5	22.5
20°-30°	431.5	23.6
30°-40°	411.6	22.5
40°-50°	265.6	14.5
50°-60°	82.5	4.5
60°-70°	12.1	0.7
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1058.9	57.8
0°-40°	1470.4	80.3
0°-60°	1818.5	99.3
0°-90°	1831.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1831.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2598	
5°	2420	216
15°	1459	411
25°	932	432
35°	662	412
45°	343	266
55°	85	82
65°	9	12
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P643609

CATALOG NUMBER: ML5615LSVWFL9FS1E - 692SC - 1500LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2598.5
2.5°	2552.5
5°	2419.9
7.5°	2209.4
10°	1956.4
12.5°	1692.8
15°	1459.3
17.5°	1277.1
20°	1133.9
22.5°	1024.2
25°	932.2
27.5°	854.4
30°	783.6
32.5°	721.7
35°	661.6
37.5°	601.4
40°	527.1
42.5°	438.7
45°	343.2
47.5°	254.7
50°	182.2
52.5°	125.6
55°	84.9
57.5°	54.8
60°	33.6
62.5°	19.5
65°	8.8
67.5°	3.5
70°	1.8
72.5°	1.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)