

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643177

Luminaire Tested: ML5615LSVWFL759FS1E - 594SNB - 900LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643177
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-79)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL759FS1E - 594SNB - 900LM - 3000K
Description: ML56 RR, 75D TIR OPTIC, 5" SATIN NICKLE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1128.4 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.09
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643177
CATALOG NUMBER: ML5615LSVWFL759FS1E - 594SNB - 900LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P643177

CATALOG NUMBER: ML5615LSVWFL759FS1E - 594SNB - 900LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91																											
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83																											
3	99	92	86	81	97	90	85	80	87	83	79	85	81	78	83	79	77	75																											
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68																											
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62																											
6	82	72	65	60	81	71	64	60	69	64	59	68	63	59	67	62	58	57																											
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52																											
8	73	62	55	50	72	61	55	50	60	54	50	59	54	50	58	53	50	48																											
9	69	58	51	47	68	57	51	46	56	50	46	55	50	46	54	50	46	44																											
10	65	54	48	43	64	54	47	43	53	47	43	52	47	43	51	46	43	41																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	58598
5°	59559
10°	61402
15°	63860
20°	64778
25°	61703
30°	55385
35°	44686
40°	30833
45°	18365
50°	11618
55°	7927
60°	6173
65°	4987
70°	4039
75°	3142
80°	1864
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18365 cd/sqm



TEST NUMBER: P643177

CATALOG NUMBER: ML5615LSVWFL759FS1E - 594SNB - 900LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.2	6.4
10°-20°	220.3	19.5
20°-30°	322.5	28.6
30°-40°	284.7	25.2
40°-50°	135.1	12.0
50°-60°	54.4	4.8
60°-70°	27.0	2.4
70°-80°	11.0	1.0
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	615.0	54.5
0°-40°	899.7	79.7
0°-60°	1089.2	96.5
0°-90°	1128.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1128.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	742	
5°	752	72
15°	781	220
25°	708	323
35°	464	285
45°	164	135
55°	58	54
65°	27	27
75°	10	11
85°	0	1
90°	0	



TEST NUMBER: P643177

CATALOG NUMBER: ML5615LSVWFL759FS1E - 594SNB - 900LM - 3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	742.3
2.5°	745.4
5°	751.6
7.5°	758.8
10°	766.0
12.5°	774.2
15°	781.4
17.5°	782.4
20°	771.1
22.5°	745.4
25°	708.4
27.5°	663.2
30°	607.6
32.5°	540.8
35°	463.7
37.5°	379.4
40°	299.2
42.5°	225.2
45°	164.5
47.5°	122.4
50°	94.6
52.5°	73.0
55°	57.6
57.5°	47.3
60°	39.1
62.5°	31.9
65°	26.7
67.5°	22.6
70°	17.5
72.5°	13.4
75°	10.3
77.5°	7.2
80°	4.1
82.5°	2.1
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)