

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643622

Luminaire Tested: ML5615LSVWFL9FS1E - 692W - 1500LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643622
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-108)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSVWFL9FS1E - 692W - 1500LM - 3000K
Description: ML56 RR, MILKY OPTIC, 6" WHITE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1620.1 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.2
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643622

CATALOG NUMBER: ML5615LSVWFL9FS1E - 692W - 1500LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P643622

CATALOG NUMBER: ML5615LSVWFL9FS1E - 692W - 1500LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89																			
2	104	97	92	87	101	95	91	86	92	88	84	89	86	83	86	83	81	79																			
3	96	88	81	76	94	87	80	76	84	79	74	81	77	73	79	75	72	70																			
4	90	80	73	67	88	79	72	67	76	71	66	74	69	65	72	68	64	63																			
5	84	73	65	60	82	72	65	60	70	64	59	68	63	58	66	62	58	56																			
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	50																			
7	73	61	54	49	72	61	53	48	59	53	48	58	52	48	57	51	47	46																			
8	69	57	49	44	67	56	49	44	55	48	44	54	48	44	53	47	43	42																			
9	64	52	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38																			
10	61	49	42	37	59	48	42	37	47	41	37	47	41	37	46	40	37	35																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	50977
5°	50732
10°	50071
15°	49234
20°	48182
25°	46956
30°	45285
35°	43165
40°	38372
45°	29034
50°	19795
55°	13610
60°	10175
65°	8509
70°	7694
75°	7117
80°	6061
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 29034 cd/sqm



TEST NUMBER: P643622

CATALOG NUMBER: ML5615LSVWFL9FS1E - 692W - 1500LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.3	5.4
10°-20°	244.3	15.1
20°-30°	356.6	22.0
30°-40°	398.3	24.6
40°-50°	289.8	17.9
50°-60°	133.2	8.2
60°-70°	66.4	4.1
70°-80°	35.0	2.2
80°-90°	9.1	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	688.1	42.5
0°-40°	1086.4	67.1
0°-60°	1509.5	93.2
0°-90°	1620.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1620.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	930	
5°	922	87
15°	868	244
25°	776	357
35°	645	398
45°	374	290
55°	142	133
65°	66	66
75°	34	35
85°	8	9
90°	0	



TEST NUMBER: P643622

CATALOG NUMBER: ML5615LSVWFL9FS1E - 692W - 1500LM - 3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	929.9
2.5°	926.7
5°	921.9
7.5°	912.3
10°	899.5
12.5°	885.1
15°	867.5
17.5°	846.7
20°	825.9
22.5°	801.9
25°	776.3
27.5°	745.9
30°	715.4
32.5°	681.8
35°	645.0
37.5°	597.0
40°	536.2
42.5°	459.4
45°	374.5
47.5°	296.1
50°	232.1
52.5°	180.9
55°	142.4
57.5°	113.6
60°	92.8
62.5°	76.8
65°	65.6
67.5°	56.0
70°	48.0
72.5°	40.0
75°	33.6
77.5°	25.6
80°	19.2
82.5°	12.8
85°	8.0
87.5°	3.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)